

Flat suction cup (round)

PFG 50 FPM-65 N008

Part no...:10.01.01.00077

<https://www.schmalz.com/10.01.01.00077>

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 50

Suction cup material: Fluorocaotchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking

Design Data



Attribute	Value
d	8 mm
d1	20 mm
Dk	29.10 mm
Dmax(S)	53.50 mm
Ds	50 mm
H	15 mm
H2	7 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	91 N
Volume	7.08 cm ³
Curve radius (min) (convex)	75 mm
Size	50
Nipple family	N 008
Suction cup material	Fluorocaotchuc FPM
Material hardness [Shore A]	65 Shore A
Weight	16.50 g

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Flat suction cup (round)

PFG 50 FPM-65 N008

Part no.:10.01.01.00077

<https://www.schmalz.com/10.01.01.00077>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N008 G1/8-AG DN350

Part no.:10.01.01.03532

Thread G1: G1/8"-M

Length L1: 22 mm

Fitting length: 5 mm

Material: Aluminum

Spanner size SW2: 4 mm



SA-NIP N008 G1/8-IG DN350

Part no.:10.01.01.03524

Thread G1: G1/8"-F

Length L1: 25 mm

Fitting length: 16 mm

Material: Aluminum

Spanner size SW2: 4 mm



SU 50

Part no.:10.01.01.12837

Size: 50

Clamping range: 45.0 ... 60.0 mm

Temperature resistance: 80 °C

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in



Flat suction cup (round)

PFG 50 FPM-65 N008

Part no...:10.01.01.00077

<https://www.schmalz.com/10.01.01.00077>

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in