

Vacuum block

VCBL-S4 120x50x50 TV

Part no...:10.01.12.02323

<https://www.schmalz.com/10.01.12.02323>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Systems from SCM / Morbidelli > Vacuum Blocks VCBL-S4 > VCBL-S4 120x50x50 TV

Vacuum block for SCM/Morbidelli console - Type 4



Dimensions (LxB): 120 x 50


Length L: 120 mm

Width B: 50 mm

Height H: 50 mm

Add. function: Sensing valve

Design Data



Attribute	Value
B	50 mm
B1	145 mm
H	50 mm
H2	27 mm
L	120 mm
L1	145 mm
L2	109 mm

Technical Data

Attribute	Value
Weight	0.52 kg

Spare parts

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Vacuum block

VCBL-S4 120x50x50 TV

Part no...:10.01.12.02323

<https://www.schmalz.com/10.01.12.02323>



VCSP-O 140x130x16.5 TPE

Part no...:10.01.12.02325

Construction use: Vacuum block

Length L: 140 mm

Width B: 130 mm

Height H: 16.5 mm



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm



VCSP-O 120x120x16.5 TPE

Part no...:10.01.12.00010

Length L: 120 mm

Width B: 120 mm

Height H: 16.5 mm

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Vacuum block

VCBL-S4 120x50x50 TV

Part no...:10.01.12.02323

<https://www.schmalz.com/10.01.12.02323>



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm




VCSP-O 120x50x15.5 TPE

Part no...:10.01.12.00012

Length L: 120 mm

Width B: 50 mm

Height H: 15.5 mm



VCDR 141x77.2x5.1 VCBL-S

Part no...:10.01.12.03138

Length L: 141 mm

Width B: 77.2 mm

Height H: 5.1 mm

Construction use: Vacuum block VCBL-S

Clamping range: mm

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it