

Starter kit

VEE STARTERSET

Part no...:10.01.36.00030

<https://www.schmalz.com/10.01.36.00030>

Home > Vacuum Technology for Automation > Vacuum Components > Area Gripping Systems and End Effectors > Vacuum End Effectors VEE > Starter Set VEE > VEE STARTERSET

120 piece starter set for setup of up to two VEE vacuum end effectors



Design Data



Technical Data

Attribute	Value
Weight	3,062.30 g
with	

Accessories

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Starter kit

VEE STARTERSET

Part no...:10.01.36.00030

<https://www.schmalz.com/10.01.36.00030>



SPI 24 PE SPB4-30

Part no...:10.01.06.02855

Size: 24

Material: Polyethylene

Use: SPB4-30



SPSE 30

Part no...:10.01.06.02953

Size: 30

Spare parts



FLAN-PL 63x11.5-UNI

Part no...:10.01.30.00017

External diameter D: 63 mm

Length L: 11.5 mm

Size: UNI

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Starter kit

VEE STARTERSET

Part no...:10.01.36.00030

<https://www.schmalz.com/10.01.36.00030>



SC 080 G3/8-AG

Part no...:10.01.06.02593

Connection geometry: 080

Vacuum connection: G3/8"-M

Length L1: 32 mm

Fitting length: 7.5 mm

Nominal diameter dn: 10.3 mm



SPB4f 30 SI-55 SC080

Part no...:10.01.06.03264

Size: 30

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 4.5



VEE-CO18-L

Part no...:10.01.36.00033

Packaging unit: 4 pieces

Starter kit

VEE STARTERSET

Part no...:10.01.36.00030

<https://www.schmalz.com/10.01.36.00030>



VEE-CO18-L-G3/8-IG

Part no...:10.01.36.00036

Thread G1: G3/8"-F

Packaging unit: 4 pieces



VEE-CO18-U

Part no...:10.01.36.00031

Packaging unit: 4 pieces



VEE-PL C

Part no...:10.01.36.00039

Shape mounting elements: closed

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Starter kit

VEE STARTERSET

Part no...:10.01.36.00030

<https://www.schmalz.com/10.01.36.00030>



VEE-QCF2

Part no...:10.01.36.00113

Type: 2



VEE-QCM 32

Part no...:10.01.36.00121

Length L1: 32 mm

Pitch diameter D mk: 46 mm

Number of holes: 8

Flow rate max.: 60 m³/h



VEE-QCM 53

Part no...:10.01.36.00122

Length L1: 53 mm

Thread G1: G1/8"-F

Pitch diameter D mk: 46 mm

Number of holes: 8

Flow rate max.: 20 m³/h

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Starter kit

VEE STARTERSET

Part no.:10.01.36.00030

<https://www.schmalz.com/10.01.36.00030>



VEE-TU 18x1.5x17.8

Part no.:10.01.36.00037

External diameter D: 18 mm

Wall thickness s: 1.5 mm

Length L: 17.8 mm



VEE-TU 18x1.5x200

Part no.:10.01.36.00038

External diameter D: 18 mm

Wall thickness s: 1.5 mm

Length L: 200 mm