

Vacuum blower

SB 235 400 3.6 IE3-TYP4

Part no.:10.04.01.00128

<https://www.schmalz.com/10.04.01.00128>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Blowers > Vacuum Blowers SB > SB 235 400 3.6 IE3-TYP4

Vacuum Blower for high suction rate



Suction rate (60 Hz): 235 m³/h

Vacuum (60 Hz): 400 mbar

Rated power 60 Hz: 3.6 kW

Voltage at 60Hz: Y575V


Construction: IE3:CAN

Permission: UL/CSA

Permission: UL/CSA

Weight: 53.5 kg

Design Data



Attribute	Value
B	390 mm
B1	452 mm
d	12 mm
D2	60 mm
G1	G2"-F
H	454 mm
L	495 mm
X1	310 mm
Y1	310 mm

Technical Data

Attribute	Value
Suction rate (60 Hz)	235 m ³ /h
Vacuum (60 Hz)	400 mbar
Protection type IP	IP 65
Rated power 60 Hz	3.60 kW
Voltage at 60Hz	Y575V
Weight	53.50 kg
Construction	IE3-TYP4
Permission	UL/CSA

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Vacuum blower

SB 235 400 3.6 IE3-TYP4

Part no...:10.04.01.00128

<https://www.schmalz.com/10.04.01.00128>

Construction	IE3:CAN
Product family	SB

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Accessories



SBB-230V-AC-ST/ABS-LUE SB

Part no...:10.04.04.00236

Construction use: Blower SB

Voltage DC: 230V - AC

Material: Steel/ABS

Thread G1: G2"-M

Length L: 661 mm

Width B: 586 mm

Height H: 625 mm



SBB-24V-DC-ST/ABS-LUE SB

Part no...:10.04.04.00321

Construction use: Blower SB

Voltage DC: 24V - DC

Material: Steel/ABS

Thread G1: G2"-M

Length L: 661 mm

Width B: 586 mm

Height H: 625 mm



STF 60 P 4.5 SSD

Part no...:10.07.01.00259

Connection: Ø60mm

Shape: Piclon housing

Nominal flow rate: 270 m³/h

Filter pore size: 3 µm

Additional function: Hose clamps SSD

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Vacuum blower

SB 235 400 3.6 IE3-TYP4

Part no...:10.04.01.00128

<https://www.schmalz.com/10.04.01.00128>



SD SB FITTING SD

Part no...:10.04.04.00363

Construction use: Blower SB

and: Silencer

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it