

Universal holder

HTR-UNI 2N G2 200

Part no.:10.01.03.00309

<https://www.schmalz.com/10.01.03.00309>




Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Holders for Suction Cups and Spring Plungers > Universal Holders HTR-UNI > HTR-UNI 2N G2 200

Universal holder for adjustable mounting of suction cups



- Suction cup connection: G1/4"-M
- Length L1: 200 mm
- Operating temperature: 0 ... 80 °C
- Cross-beam connection: 2 T-slots

Design Data



Attribute	Value
B	44 mm
D	59 mm
G1	G1/4"-M
G2	M6-M
G3	G1/4"-F
H	27.50 mm
L	30 mm
L1	200 mm
L2	190 mm
L3	20 mm
L4	126 mm
LG2	6 mm
W	15 °

Technical Data

Attribute	Value
Weight	222.10 g
Product family	HTR-UNI

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Universal holder

HTR-UNI 2N G2 200

Part no.:10.01.03.00309

<https://www.schmalz.com/10.01.03.00309>

Accessories



STV-GE G1/4-AG 10

Part no.:10.08.02.00251

Thread G1: G1/4"-M

Hose diameter: 10 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 16.5 mm

Length L: 23.4 mm



STV-GE G1/4-AG 12

Part no.:10.08.02.00208

Thread G1: G1/4"-M

Hose diameter: 12 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 19.5 mm

Length L: 29 mm



STV-GE G1/4-AG 8

Part no.:10.08.02.00207

Thread G1: G1/4"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 13.9 mm

Length L: 17.8 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Universal holder

HTR-UNI 2N G2 200

Part no.:10.01.03.00309

<https://www.schmalz.com/10.01.03.00309>



STV-GE G1/4-AG 6

Part no.:10.08.02.00205

Thread G1: G1/4"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11.2 mm

Length L: 15.2 mm



SAUG-ANB G1/4-AG 80

Part no.:10.01.03.00292

Suction cup connection: G1/4"-M

Length L: 80 mm

Spare parts



SAUG-ANB G1/4-AG 200

Part no.:10.01.03.00308

Suction cup connection: G1/4"-M

Length L: 200 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8562431
schmalz@schmalz.co.kr