

Universal holder

HTR-UNI 2N X3

Part no.:10.01.03.00302

<https://www.schmalz.com/10.01.03.00302>



Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Holders for Suction Cups and Spring Plungers > Universal Holders HTR-UNI > HTR-UNI 2N X3

Universal holder for adjustable mounting of suction cups




Suction cup connection: ball head 28.5 mm

Operating temperature: °C

Cross-beam connection: 2 T-slots

Design Data



Attribute	Value
B	44 mm
D	59 mm
G2	M6-M
H	27.50 mm
L3	20 mm
LG2	6 mm

Technical Data

Attribute	Value
Weight	121.70 g
Product family	HTR-UNI

Accessories

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Universal holder

HTR-UNI 2N X3

Part no.:10.01.03.00302

<https://www.schmalz.com/10.01.03.00302>



HTR-FST A3 FSTI

Part no.:10.01.03.06136

Cross-beam connection: Ball head 28.5 mm

Thread G1: M18x1.5-IG

Construction use: Spring plunger



HTR-S A3 RA

Part no.:10.01.10.00239

Suction cup connection: Rectangular ada

Vacuum connection: G1/4"-F



HTS-A3 D SGM 50/70 OP

Part no.:10.01.17.00583

Connection 1: Ball head 28.5 mm

Construction use: Magnetic gripper

Size: 50/70

Shape: Double block

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Universal holder

HTR-UNI 2N X3

Part no.:10.01.03.00302

<https://www.schmalz.com/10.01.03.00302>



HTS-A3 SGM 30/40 OP

Part no.:10.01.17.00558

Connection 1: Ball head 28.5 mm

Construction use: Magnetic gripper

Size: 30/40



HTS-A3 D SGM 30/40 OP

Part no.:10.01.17.00582

Connection 1: Ball head 28.5 mm

Construction use: Magnetic gripper

Size: 30/40

Shape: Double block



HTS-A3 SGM 50/70 OP

Part no.:10.01.17.00576

Connection 1: Ball head 28.5 mm

Construction use: Magnetic gripper

Size: 50/70

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8962431
schmalz@schmalz.co.kr

Universal holder

HTR-UNI 2N X3

Part no.:10.01.03.00302

<https://www.schmalz.com/10.01.03.00302>



HTS-A3 SNG AP/AE OP

Part no.:10.01.29.00619

Pressure range (operating pressure): bar

Length L: 38 mm

Width B: 15 mm

Height H: 9.4 mm

Construction use: Needle gripper

Size: AP/AE

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr