

Bellows suction cups (round)

SPB1 50 ED-65 G1/4-IG

Part no.:10.01.06.03501

<https://www.schmalz.com/10.01.06.03501>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > Bellows Suction Cups SPB1 (1.5 Folds) > SPB1 50 ED-65 G1/4-IG

Bellows suction cup (round) for very uneven workpieces



Size: 50


Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/4"-F

Number of folds: 1.5

Design Data



Attribute	Value
d2	32.30 mm
dn	6.10 mm
Dmax(S)	58.40 mm
Ds	51.40 mm
G1	G1/4"-F
H	49.20 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	18 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	54.70 N
Pull-off force	72.70 N
Lateral force	31.20 N
Volume	30.18 cm ³
Curve radius (min) (convex)	40 mm
Hose diameter (rec.) d	6 mm
Size	50
Number of folds	1.50

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Bellows suction cups (round)

SPB1 50 ED-65 G1/4-IG

Part no.:10.01.06.03501

<https://www.schmalz.com/10.01.06.03501>

Suction cup material	Elastodur ED
Material hardness [Shore A]	65 Shore A
Weight	27.10 g
Product family	SPB1

Accessories



SIEB 17.5x0.8 MS-A2 280 0.28/0.16

Part no.:10.07.01.00308

External diameter D: 17.5 mm

Length L: 0.8 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm



SPI 40 PA SPB1-50

Part no.:10.01.06.03388

Size: 40

Material: Polyamide

Use: SPB1-50

Spare parts

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Bellows suction cups (round)

SPB1 50 ED-65 G1/4-IG

Part no.:10.01.06.03501

<https://www.schmalz.com/10.01.06.03501>



SC 050 G1/4-IG MOD

Part no.:10.01.06.02488

Connection geometry: 050

Connection: G1/4"-F

Length L1: 26.5 mm

Fitting length: 17.2 mm

Nominal diameter dn: 6.1 mm



SPB1 50 ED-65 SC050

Part no.:10.01.06.02456

Size: 50

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Number of folds: 1.5

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624831
schmalz@schmalz.co.kr