

## Bellows suction cups (round)

SFB1 25 NBR-ESD-55 G1/8-IG

Part no.:10.01.06.04795

<https://www.schmalz.com/10.01.06.04795>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Suction Cups SFF / SFB1 > SFB1 25 NBR-ESD-55 G1/8-IG

### Bellows suction cup (round) for very uneven workpieces flexible workpieces




Size: 25

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5

### Design Data



| Attribute  | Value    |
|------------|----------|
| G1         | G1/8"-F  |
| Dmax(S)    | 26.50 mm |
| Ds         | 25 mm    |
| dn         | 4.10 mm  |
| LG1        | 8 mm     |
| H          | 33.20 mm |
| SW1        | 14 mm    |
| Z (Stroke) | 6.50 mm  |

### Technical Data

| Attribute                   | Value                  |
|-----------------------------|------------------------|
| Size                        | 25                     |
| Suction cup material        | Nitrile rubber NBR-ESD |
| Suction force (-600mbar)    | 3.20 N                 |
| Product family              | SFB1                   |
| Volume                      | 1.90 cm <sup>3</sup>   |
| Number of folds             | 1.50                   |
| Material hardness [Shore A] | 55 Shore A             |

### Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031  
schmalz@schmalz.co.kr

## Bellows suction cups (round)

SFB1 25 NBR-ESD-55 G1/8-IG

Part no.:10.01.06.04795

<https://www.schmalz.com/10.01.06.04795>

### Spare parts



#### SFB1 25 NBR-ESD-55 SC040

Part no.:10.01.06.04714

Size: 25

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5



#### SC 040 G1/8-IG

Part no.:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20.7 mm

Fitting length: 14 mm

Nominal diameter dn: 4.1 mm

### Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031  
schmalz@schmalz.co.kr