

Vacuum block

VCBL-K2 130x30x100 L

Part no.:10.01.12.00855

<https://www.schmalz.com/10.01.12.00855>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for 2-Circuit Systems > Vacuum Blocks VCBL-K2 > VCBL-K2 130x30x100 L

Vacuum block for Schmalz 2-circuit console




Dimensions (LxB): 130 x 30

Dimension suction plate bottom: 140x115 mm

Height H: 100 mm

Arrangement: longways

Design Data



Attribute	Value
B	30 mm
H	100 mm
H2	63 mm
L	130 mm
L1	149 mm
L2	16 mm

Technical Data

Attribute	Value
Dimension suction plate bottom	140x115 mm
Weight	0.63 kg

Spare parts

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Vacuum block

VCBL-K2 130x30x100 L

Part no.:10.01.12.00855

<https://www.schmalz.com/10.01.12.00855>



VCDR 130x30x9

Part no.:10.01.12.00804

Length L: 130 mm

Width B: 30 mm

Height H: 9 mm



REIB-PL 116x19.5x5.5 TPE

Part no.:10.01.12.00805

Construction use: Vacuum block

Length L: 116 mm

Width B: 19.5 mm

Height H: 5.5 mm

Size: 130x30



ERS VCBL-Einleger

Part no.:10.01.12.00618

Construction use: Vacuum block

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr

Vacuum block

VCBL-K2 130x30x100 L

Part no.:10.01.12.00855

<https://www.schmalz.com/10.01.12.00855>



VCSP-U 140x115x16.5 VCBL-K2 TPE

Part no.:10.01.12.00798

Length L: 140 mm

Width B: 115 mm

Height H: 16.5 mm



VST VCSP

Part no.:10.01.12.00723

Construction use: Suction plate vacuum block

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8562431
schmalz@schmalz.co.kr