

Hose clamp

SSB 16-27 ST-VZ

Part no.:10.07.10.00002

<https://www.schmalz.com/10.07.10.00002>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Hose Clamps SSB / SSD > SSB 16-27 ST-VZ

Hose clamp for securing smooth hoses




Clamping range: 16.0 ... 27.0 mm

Material: Steel

Surface: galvanised

Design Data



Attribute	Value
d1	16 mm
d2	27 mm
L	9 mm

Technical Data

Attribute	Value
Clamping range	16.0 ... 27.0 mm
Material	Steel
Weight	14 g
Product family	SSB / SSD

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr

Hose clamp

SSB 16-27 ST-VZ

Part no.:10.07.10.00002

<https://www.schmalz.com/10.07.10.00002>

Accessories



KAPP 9 Band

Part no.:20.12.01.00036

Length L: 9 mm

Size: Band



VSL 19-13 PVC-DS KL-TR

Part no.:10.07.09.00016

External diameter D: 19 mm

Internal diameter d: 13 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 85 mm

Pressure range (operating pressure): -0.90 ... 5.00 bar

Operating temperature: -15 ... 65 °C



VSL 21-12 PVC-G KL-TR

Part no.:10.07.09.00006

External diameter D: 21 mm

Internal diameter d: 12 mm

Length max.: 50 m

Material hose: PVC with tissue

Pressure range (operating pressure): bar

Operating temperature: °C

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Hose clamp

SSB 16-27 ST-VZ

Part no.:10.07.10.00002

<https://www.schmalz.com/10.07.10.00002>



VSL 26-19 PVC-DS KL-TR

Part no.:10.07.09.00007

External diameter D: 26 mm

Internal diameter d: 19 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 85 mm

Pressure range (operating pressure): -0.90 ... 5.00 bar

Operating temperature: -15 ... 65 °C

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8162431
schmalz@schmalz.co.kr