

Suction cup connection nipple (inst)

SA-NIP N009 G1/4-AG

Part no.:10.01.01.10097

<https://www.schmalz.com/10.01.01.10097>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SA-NIP N009 G1/4-AG

Suction cup connection nipple pre-assembly




Thread G1: G1/4"-M

Length L1: 25 mm

Material: Aluminum

Design Data



Attribute	Value
dn	5.50 mm
G1	G1/4"-M
G2	M10x1,25-M
L	5 mm
L1	25 mm
LG1	10 mm
SW1	17 mm

Technical Data

Attribute	Value
Nipple family	N 009
Material	Aluminum
Weight	9.20 g

Accessories

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Suction cup connection nipple (inst)

SA-NIP N009 G1/4-AG

Part no.:10.01.01.10097

<https://www.schmalz.com/10.01.01.10097>



PFG 60 FPM-65 N009 M10x1.25-IG

Part no.:10.01.01.00078

Size: 60

Suction cup material: Fluorocautchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking



PFG 60 HT1-60 N009 M10x1.25-IG

Part no.:10.01.01.11169

Size: 60

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking



PFG 60 NBR-55 N009 M10x1.25-IG

Part no.:10.01.01.00018

Size: 60

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Suction cup connection nipple (inst)

SA-NIP N009 G1/4-AG

Part no.:10.01.01.10097

<https://www.schmalz.com/10.01.01.10097>



PFG 60 PU-55 N009 M10x1.25-IG

Part no.:10.01.01.00058

Size: 60

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A



PFG 60 SI-55 N009 M10x1.25-IG

Part no.:10.01.01.00038

Size: 60

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible



PFG 80 FPM-65 N009 M10x1.25-IG

Part no.:10.01.01.00079

Size: 80

Suction cup material: Fluorocautchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8162431
schmalz@schmalz.co.kr

Suction cup connection nipple (inst)

SA-NIP N009 G1/4-AG

Part no.:10.01.01.10097

<https://www.schmalz.com/10.01.01.10097>



PFG 80 HT1-60 N009 M10x1.25-IG

Part no.:10.01.01.11170

Size: 80

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking



PFG 80 NBR-55 N009 M10x1.25-IG

Part no.:10.01.01.00019

Size: 80

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A



PFG 80 PU-55 N009 M10x1.25-IG

Part no.:10.01.01.00059

Size: 80

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8524031
schmalz@schmalz.co.kr

Suction cup connection nipple (inst)

SA-NIP N009 G1/4-AG

Part no.:10.01.01.10097

<https://www.schmalz.com/10.01.01.10097>



PFG 80 SI-55 N009 M10x1.25-IG

Part no.:10.01.01.00039

Size: 80

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible



PFG 95 FPM-65 N009 M10x1.25-IG

Part no.:10.01.01.00080

Size: 95

Suction cup material: Fluorocaotchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking



PFG 95 NBR-55 N009 M10x1.25-IG

Part no.:10.01.01.00020

Size: 95

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Suction cup connection nipple (inst)

SA-NIP N009 G1/4-AG

Part no.:10.01.01.10097

<https://www.schmalz.com/10.01.01.10097>



PFG 95 PU-55 N009 M10x1.25-IG

Part no.:10.01.01.00060

Size: 95

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A



PFG 95 SI-55 N009 M10x1.25-IG

Part no.:10.01.01.00040

Size: 95

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8524031
schmalz@schmalz.co.kr