

Suction cup connection nipple

SA-NIP N007 G1/8-IG DN350

Part no.:10.01.01.03523

<https://www.schmalz.com/10.01.01.03523>

Suction cup connection nipple



Nipple family: N 007

Thread G1: G1/8"-F

Length L1: 24.5 mm

Length L: 16 mm


Fitting length: 16 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Spanner size SW2: 4 mm

Design Data



Attribute	Value
dn	3.50 mm
D	10 mm
D2	6.50 mm
G1	G1/8"-F
L	16 mm
L1	24.50 mm
L2	7 mm
L3	1.50 mm
LG1	9 mm
SW1	14 mm
SW2	4 mm

Technical Data

Attribute	Value
Nipple family	N 007
Material	Aluminum
Weight	5.80 g

Accessories

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Suction cup connection nipple

SA-NIP N007 G1/8-IG DN350

Part no.:10.01.01.03523

<https://www.schmalz.com/10.01.01.03523>



PFG 25 FPM-65 N007

Part no.:10.01.01.00073

Size: 25

Suction cup material: Fluorocautchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking



PFG 25 HT1-60 N007

Part no.:10.01.01.11164

Size: 25

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking



PFG 25 NBR-CO-55 N007

Part no.:10.01.01.10338

Size: 25

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Suction cup connection nipple

SA-NIP N007 G1/8-IG DN350

Part no.:10.01.01.03523

<https://www.schmalz.com/10.01.01.03523>



PFG 25 NBR-55 N007

Part no.:10.01.01.00013

Size: 25

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A



PFG 25 PU-55 N007

Part no.:10.01.01.00053

Size: 25

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A



PFG 25 SI-55 N007

Part no.:10.01.01.00033

Size: 25

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8562431
schmalz@schmalz.co.kr

Suction cup connection nipple

SA-NIP N007 G1/8-IG DN350

Part no.:10.01.01.03523

<https://www.schmalz.com/10.01.01.03523>



PFG 30 FPM-65 N007

Part no.:10.01.01.00074

Size: 30

Suction cup material: Fluorocautchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking



PFG 30 HT1-60 N007

Part no.:10.01.01.11165

Size: 30

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking



PFG 30 NBR-CO-55 N007

Part no.:10.01.01.10339

Size: 30

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8524031
schmalz@schmalz.co.kr

Suction cup connection nipple

SA-NIP N007 G1/8-IG DN350

Part no.:10.01.01.03523

<https://www.schmalz.com/10.01.01.03523>




PFG 30 NBR-55 N007

Part no.:10.01.01.00014

Size: 30

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A



PFG 30 PU-55 N007

Part no.:10.01.01.00054

Size: 30

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A



PFG 30 SI-55 N007

Part no.:10.01.01.00034

Size: 30

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Suction cup connection nipple

SA-NIP N007 G1/8-IG DN350

Part no.:10.01.01.03523

<https://www.schmalz.com/10.01.01.03523>



PFG 35 FPM-65 N007

Part no.:10.01.01.00075

Size: 35

Suction cup material: Fluorocautchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking



PFG 35 HT1-60 N007

Part no.:10.01.01.11166

Size: 35

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking



PFG 35 NBR-CO-55 N007

Part no.:10.01.01.10340

Size: 35

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8524031
schmalz@schmalz.co.kr

Suction cup connection nipple

SA-NIP N007 G1/8-IG DN350

Part no.:10.01.01.03523

<https://www.schmalz.com/10.01.01.03523>



PFG 35 PU-55 N007

Part no.:10.01.01.00055

Size: 35

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A



PFG 35 SI-55 N007

Part no.:10.01.01.00035

Size: 35

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible



PFG 40 FPM-65 N007

Part no.:10.01.01.00076

Size: 40

Suction cup material: Fluorocautchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Suction cup connection nipple

SA-NIP N007 G1/8-IG DN350

Part no.:10.01.01.03523

<https://www.schmalz.com/10.01.01.03523>



PFG 40 HT1-60 N007

Part no.:10.01.01.11167

Size: 40

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking



PFG 40 NBR-CO-55 N007

Part no.:10.01.01.10341

Size: 40

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A



PFG 40 NBR-55 N007

Part no.:10.01.01.00016

Size: 40

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Contact Schmalz


Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624831
schmalz@schmalz.co.kr

Suction cup connection nipple

SA-NIP N007 G1/8-IG DN350

Part no.:10.01.01.03523

<https://www.schmalz.com/10.01.01.03523>



PFG 40 PU-55 N007

Part no.:10.01.01.00056

Size: 40

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A



PFG 40 SI-55 N007

Part no.:10.01.01.00036

Size: 40

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624931
schmalz@schmalz.co.kr