

Bellows suction pad (round)

SFB1 25 NBR-ESD-55 SC040

Part no.:10.01.06.04714

<https://www.schmalz.com/10.01.06.04714>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > SFB1 25 NBR-ESD-55 SC040

Bellows suction cup (round) with 1.5 corr. for dynamic handling workpieces




Size: 25

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5

Design Data



Attribute	Value
D1	18.80 mm
Dmax(S)	26.50 mm
Dk	13 mm
Ds	25 mm
d	7.50 mm
d1	10.40 mm
d2	8.20 mm
H	19.20 mm
H2	4.70 mm
Z (Stroke)	6.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	3.20 N
Volume	1.88 cm ³
Size	25
Number of folds	1.50
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A
Curve radius (min) (convex)	18 mm
Nipple family	SC 040

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Bellows suction pad (round)

SFB1 25 NBR-ESD-55 SC040

Part no.:10.01.06.04714

<https://www.schmalz.com/10.01.06.04714>

Weight	2 g
Product family	SFB1

Accessories



SC 040 G1/8-AG

Part no.:10.01.06.02490

Connection geometry: 040
Connection: G1/8"-M
Length L1: 20.2 mm
Fitting length: 6 mm
Nominal diameter dn: 4.1 mm



SC 040 G1/8-IG

Part no.:10.01.06.02482

Connection geometry: 040
Connection: G1/8"-F
Length L1: 20.7 mm
Fitting length: 14 mm
Nominal diameter dn: 4.1 mm

Spare parts

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr

Bellows suction pad (round)

SFB1 25 NBR-ESD-55 SC040

Part no.:10.01.06.04714

<https://www.schmalz.com/10.01.06.04714>



SC 040 M5-AG

Part no.:10.01.06.04346

Connection geometry: 040

Vacuum connection: M5-M

Fitting length: 5 mm

Nominal diameter dn: 1.8 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8624311
schmalz@schmalz.co.kr