

Suction plate (round)

SPC 250 NBR-55 G1/2-IG

Part no.:10.01.01.01189

<https://www.schmalz.com/10.01.01.01189>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Wood > Suction Plates SPC
> SPC 250 NBR-55 G1/2-IG

Suction plate (round) with separation function for porous workpieces




Size: 250

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Connection: G1/2-IG

Design Data



Attribute	Value
d	34 mm
d2	203 mm
d3	178 mm
ds	33.50 mm
Dmax(S)	263 mm
Ds	252 mm
G1	G1/2"-F
G2	G1/2"-F
H	25 mm
H1	26.50 mm
L2	76 mm
LG1	13.50 mm
LG2	15 mm
Z (Stroke)	6.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	2540 N
Volume	387.99 cm ³
Hose diameter (rec.) d	12 mm

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Suction plate (round)

SPC 250 NBR-55 G1/2-IG

Part no...:10.01.01.01189

<https://www.schmalz.com/10.01.01.01189>

Size	250
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	1330 g
Number of folds	0
Product family	SPC

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



PC 250

Part no...:10.01.01.13090

Size: 250

Spare parts



DR-SPC 33 HNBR-65

Part no...:10.01.01.11371

Size: 33

Suction cup material: Hydr. nitril rubber HNBR

Material hardness [Shore A]: 65 Shore A

Height H: 16.5 mm

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Suction plate (round)

SPC 250 NBR-55 G1/2-IG

Part no...:10.01.01.01189

<https://www.schmalz.com/10.01.01.01189>



DR-SPC 250 NBR-55

Part no...:10.01.01.01192

Size: 250

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Height H: 24.5 mm