

Bellows suction cup SI-HD (round)

FG 9 SI-HD-65 N016

Part no.:10.01.06.03148

<https://www.schmalz.com/10.01.06.03148>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FG 9 SI-HD-65 N016

Bellows suction cup (round)for wear-resistant handling



Size: 9


Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Material characteristics: FDA-compatible

Number of folds: 2.5

Design Data



Attribute	Value
d	4.50 mm
d2	4.10 mm
D1	8.90 mm
Dk	9 mm
Dmax(S)	9.50 mm
Ds	9 mm
H	15 mm
H2	3.80 mm
H3	8.20 mm
Z (Stroke)	3 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	0.68 N
Pull-off force	2.30 N
Volume	0.30 cm ³
Curve radius (min) (convex)	10 mm
Hose diameter (rec.) d	4 mm
Size	9
Nipple family	N 016

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bellows suction cup SI-HD (round)

FG 9 SI-HD-65 N016

Part no...:10.01.06.03148

<https://www.schmalz.com/10.01.06.03148>

Number of folds	2.50
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A
Weight	0.60 g
Product family	FG

Accessories



SA-NIP N016 G1/8-AG DN350

Part no...:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N016 G1/8-IG DN350

Part no...:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 12 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bellows suction cup SI-HD (round)

FG 9 SI-HD-65 N016

Part no...:10.01.06.03148

<https://www.schmalz.com/10.01.06.03148>



SA-NIP N016 M5-AG DN250

Part no...:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Material: Aluminum



SA-NIP N016 G1/8-AG DN310

Part no...:10.01.06.04062

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3.1 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel



SA-NIP N016 M5-AG DN250

Part no...:10.01.06.04365

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bellows suction cup SI-HD (round)

FG 9 SI-HD-65 N016

Part no...:10.01.06.03148

<https://www.schmalz.com/10.01.06.03148>



SA-NIP N016 M5-IG DN310

Part no...:10.01.06.04689

Nipple family: N 016

Thread G1: M5-F

Length L1: 16 mm

Fitting length: 10 mm

Nominal diameter dn: 3.1 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel



SA-NIP N016 G1/8-IG DN310

Part no...:10.01.06.04690

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 12 mm

Nominal diameter dn: 3.1 mm

Material: Aust. Stainless steel