

## Bellows suction cups (round)

FSG 18 NBR-55 M5-AG

Part no.:10.01.06.00027

<https://www.schmalz.com/10.01.06.00027>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSG (2.5 Folds) > FSG 18 NBR-55 M5-AG

### Bellows suction cup (round) for very uneven workpieces



Size: 18

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: M5-M

Number of folds: 2.5

Vacuum connection: M5-M

### Design Data



| Attribute  | Value    |
|------------|----------|
| d2         | 8 mm     |
| dn         | 2.50 mm  |
| Dmax(S)    | 19 mm    |
| Ds         | 17.20 mm |
| G1         | M5-M     |
| H          | 27.60 mm |
| LG1        | 5 mm     |
| SW1        | 7 mm     |
| Z (Stroke) | 9 mm     |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

| Attribute                   | Value                |
|-----------------------------|----------------------|
| Suction cup material        | Nitrile rubber NBR   |
| Material hardness [Shore A] | 55 Shore A           |
| Size                        | 18                   |
| Number of folds             | 2.50                 |
| Connection                  | M5-AG                |
| Curve radius (min) (convex) | 20 mm                |
| Volume                      | 1.35 cm <sup>3</sup> |

### Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | [schmalz@schmalz.pl](mailto:schmalz@schmalz.pl)

## Bellows suction cups (round)

FSG 18 NBR-55 M5-AG

Part no.:10.01.06.00027

<https://www.schmalz.com/10.01.06.00027>

|                          |        |
|--------------------------|--------|
| Suction force (-600mbar) | 3.02 N |
| Pull-off force           | 8.50 N |
| Hose diameter (rec.) d   | 2 mm   |
| Weight                   | 2.90 g |
| Product family           | FSG    |

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

### Accessories



#### SPI 17 PEEK

Part no.:10.01.06.03283

Size: 17

Material: Polyetheretherketon

### Spare parts



#### SA-NIP N016 M5-AG DN250

Part no.:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Material: Aluminum

### Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | [schmalz@schmalz.pl](mailto:schmalz@schmalz.pl)

## Bellows suction cups (round)

FSG 18 NBR-55 M5-AG

Part no...:10.01.06.00027

<https://www.schmalz.com/10.01.06.00027>



### FG 18 NBR-55 N016

Part no...:10.01.06.00053

Size: 18

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 2.5