

Mounting profile

MO-PROF 25x30x3000 1TN AL

Part no...:26.07.01.00498

<https://www.schmalz.com/26.07.01.00498>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Modular Gripper System PXT > Mounting Profiles MO-PROF PXT > MO-PROF 25x30x3000 1TN AL

Aluminium profile for construction of vacuum-gripping systems




Length L: 3,000 mm

Width B: 25 mm

Height H: 30 mm

Form: with 1 T-slot

Design Data



Attribute	Value
B	25 mm
d	3.50 mm
H	30 mm
L	3000 mm

Technical Data

Attribute	Value
Material	Aluminum
Form	with 1 T-slot
Weight	2,236.70 g

Accessories

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Mounting profile

MO-PROF 25x30x3000 1TN AL

Part no...:26.07.01.00498

<https://www.schmalz.com/26.07.01.00498>



ROHR-ENTGR VEE

Part no...:10.01.36.00043

Construction use: Vacuum end effector



ROHR-ENTGR PXT

Part no...:10.01.49.00079



HP-HT 2M8 56 HT-A3

Part no...:10.07.06.00733

Shape: Universal holder

Connection profile: 2x screws M8

Width B: 56 mm

Construction use: Holder tooling ball head 28.5

Mounting profile

MO-PROF 25x30x3000 1TN AL

Part no...:26.07.01.00498

<https://www.schmalz.com/26.07.01.00498>



HP-SE-U 1M6 12/18

Part no...:10.07.06.00719

Connection profile: 1x screw M6

Internal diameter d: 12 mm

Internal diameter d1: 18 mm



HP-FST 2M6 35 M18x1.5

Part no...:10.07.06.00722

Connection profile: 2x screws M6

Width B: 35 mm

Thread G: M18x1.5



HP-FST 2M6 35 M20x1.5

Part no...:10.07.06.00723

Connection profile: 2x screws M6

Width B: 35 mm

Thread G: M20x1.5

Mounting profile

MO-PROF 25x30x3000 1TN AL

Part no...:26.07.01.00498

<https://www.schmalz.com/26.07.01.00498>



HP-SG 2M6 E 35 G1/4-AG

Part no...:10.07.06.00712

Connection profile: 2x screws M6

Width B: 35 mm

Suction cup connection: G1/4"-M



HP-SG 2M6 E 35 G3/8-AG

Part no...:10.07.06.00715

Connection profile: 2x screws M6

Width B: 35 mm

Suction cup connection: G3/8"-M



HP-SG 2M6 E 35 G1/4-IG

Part no...:10.07.06.00716

Connection profile: 2x screws M6

Width B: 35 mm

Suction cup connection: G1/4"-F

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Mounting profile

MO-PROF 25x30x3000 1TN AL

Part no...:26.07.01.00498

<https://www.schmalz.com/26.07.01.00498>



HP-SG 2M6 E 35 G3/8-IG

Part no...:10.07.06.00717

Connection profile: 2x screws M6

Width B: 35 mm

Suction cup connection: G3/8"-F