

Compact-Terminal

SCTSi-IOL 8

Part no...:10.02.02.06592

<https://www.schmalz.com/10.02.02.06592>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Compact Terminals > Compact Terminals SCTSi IO-Link
> SCTSi-IOL 8

Modular Manifold with of up to 16 SCPSi



Communication: IO-Link

Number of ejectors: 8

Ejector type 1: SCPSt 15 G02 NO

Design Data

Contact Schmalz


Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0115 | schmalz@schmalz.com.tr

Compact-Terminal

SCTSi-IOL 8

Part no...:10.02.02.06592

<https://www.schmalz.com/10.02.02.06592>



Attribute	Value
B	97.30 mm
B1	124.70 mm
B2	13.50 mm
B3	109 mm
B4	77 mm
d	6 mm
G1	G1/8"-F
G2	G1/4"-F
G3	M12x1-M
G4	M12x1-M
G5	M12x1-F
H	105 mm
H2	91.50 mm
H3	56.50 mm
H4	22.50 mm
L	200.70 mm
L1	234.70 mm
L2	27 mm
L3	18.50 mm
L4	16 mm
L5	27 mm
X1	217.70 mm
Y1	64 mm

Technical Data

Attribute	Value
Communication	IO-Link
Weight	1.96 kg

Accessories

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0121 | schmalz@schmalz.com.tr

Compact-Terminal

SCTSi-IOL 8

Part no...:10.02.02.06592

<https://www.schmalz.com/10.02.02.06592>



VFI CN8/6 50

Part no...:10.07.01.00245

Connection: Hose 8/6 with Cap nut

Filter pore size: 50 µm



VFT G1/8-IG 80

Part no...:10.07.01.00116

Connection: G1/8"-F

Shape: Short filter insert

Nominal flow rate: 45 l/min

Nominal flow rate: 2.7 m³/h

Filter pore size: 80 µm



SET SCPS

Part no...:10.02.02.04343

Length L: 113 mm

Width B: 70 mm

Height H: 73 mm

Construction use: Compact ejectors SCPS/SCPSi

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 310 0116 | schmalz@schmalz.com.tr

Compact-Terminal

SCTSi-IOL 8

Part no...:10.02.02.06592

<https://www.schmalz.com/10.02.02.06592>



ABL-SET SCPSt einstufig


Part no...:10.02.02.05661

Width B: 18 mm

Length L: 37.5 mm

Construction use: Compact ejectors SCPSt

Size: einstufig



HUT-SN-KL 75x18x9 SCPS

Part no...:10.02.02.04149

Length L: 75 mm

Width B: 18 mm

Height H: 9 mm

Construction use: Compact ejectors SCPS/SCPSi



ASK B-M12-5 1000 S-M12-5

Part no...:21.04.05.00158

Pressure range (operating pressure): bar

Electrical connection: Fem connect M12, 5 pol

Cable length: 1,000 mm

Material hose: PUR cable

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0125 | schmalz@schmalz.com.tr

Compact-Terminal

SCTSi-IOL 8

Part no.:10.02.02.06592

<https://www.schmalz.com/10.02.02.06592>



ASK B-M12-5 2000 S-M12-5

Part no.:21.04.05.00211

Pressure range (operating pressure): bar

Electrical connection: Fem connect M12, 5 pol

Cable length: 2,000 mm

Material hose: PUR cable



ASK B-M12-5 5000 S-M12-5

№ детали.:21.04.05.00266

Cable length: 5,000 mm

Material hose: PUR cable

Запасные части



SD-EINS 15x16.5 SD

№ детали.:10.02.02.04141

Construction use: Silencer

External diameter D: 15 mm

Length L: 16.5 mm

Contact Schmalz


Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0115 | schmalz@schmalz.com.tr

Compact-Terminal

SCTSi-IOL 8

Part no...:10.02.02.06592

<https://www.schmalz.com/10.02.02.06592>



SIEB 11x2 X-5 0.415/0.22

№ детали.:10.02.02.04404

External diameter D: 11 mm

Length L: 2 mm

Material: Stainless steel X5 CrNi



VST SCPS-einstuf-SD

№ детали.:10.02.02.04737

Construction use: Compact ejectors SCPS/SCPSi

Size: einstuf-SD

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0125 | schmalz@schmalz.com.tr