

Flat suction cup (oval)

SGON 15x5 NBR-55 M5-AG

Part no.:10.01.05.00106

<https://www.schmalz.com/10.01.05.00106>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > Flat Suction Cups SGON > SGON 15x5 NBR-55 M5-AG

Flat suction cup (oval) for long and also curved workpieces



Dimensions (LxB): 15 x 5


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: M5-M

Design Data



Attribute	Value
Bmax(S)	5.50 mm
Bs	5 mm
dn	1.20 mm
G1	M5-M
H	17 mm
LG1	5 mm
Lmax(S)	15.50 mm
Ls	15 mm
SW1	8 mm
Z (Stroke)	0.70 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Technical Data

Attribute	Value
Suction force (-600mbar)	3.10 N
Volume	0.18 cm ³
Curve radius (min) (convex)	4 mm
Hose diameter (rec.) d	2 mm
Dimensions (LxB)	15 x 5
Number of folds	0
Suction cup material	Nitrile rubber NBR

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (oval)

SGON 15x5 NBR-55 M5-AG

Part no.:10.01.05.00106

<https://www.schmalz.com/10.01.05.00106>

Material hardness [Shore A] 55 Shore A

Weight 3.40 g

Product family SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N021 M5-AG DN200

Part no.:10.01.05.00126

Thread G1: M5-M

Length L1: 15.5 mm

Fitting length: 5 mm

Nominal diameter dn: 2 mm

Material: Aluminum



SA-NIP N021 M5-IG DN200

Part no.:10.01.05.00125

Thread G1: M5-F

Length L1: 15.5 mm

Fitting length: 10 mm

Nominal diameter dn: 2 mm

Material: Aluminum

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (oval)

SGON 15x5 NBR-55 M5-AG

Part no...:10.01.05.00106

<https://www.schmalz.com/10.01.05.00106>



SGO 15x5 NBR-55 N021

Part no...:10.01.05.00071

Dimensions (LxB): 15 x 5

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de