

Flange extension VEE-FE

VEE-FE 25.4x131.5

Part no...:10.01.36.00109

<https://www.schmalz.com/10.01.36.00109>

Home > Vacuum Technology for Automation > Vacuum Components > Area Gripping Systems and End Effectors > Vacuum End Effectors VEE > Flange Extensions VEE-FE > VEE-FE 25.4x131.5

Flange extension




External diameter D: 25.4 mm

Length L1: 131.5 mm

Extension to: 100 mm

Design Data



Attribute	Value
D	25.40 mm
D1	55 mm
Dmk	46 mm
G2	M4-M
L1	131.50 mm
L	118.50 mm
LG2	6.40 mm

Accessories

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flange extension VEE-FE

VEE-FE 25.4x131.5

Part no...:10.01.36.00109

<https://www.schmalz.com/10.01.36.00109>



VEE-FE-A 20

Part no...:10.01.36.00132

Flow rate max.: 20 m³/h



VEE-FE-A 60

Part no...:10.01.36.00133

Flow rate max.: 60 m³/h



VEE-RU 55x55 20 FL

Part no...:10.01.36.00090

External diameter D1: 55 mm

Length L1: 55 mm

Nominal flow rate: 20 m³/h

Pitch diameter D mk: 46 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flange extension VEE-FE

VEE-FE 25.4x131.5

Part no.:10.01.36.00109

<https://www.schmalz.com/10.01.36.00109>



VEE-RU 55x65 60 FL

Part no.:10.01.36.00065

External diameter D1: 55 mm

Length L1: 65 mm

Nominal flow rate: 60 m³/h

Pitch diameter D mk: 46 mm



RFBP 50 50 BA SPB2

Part no.:10.01.45.00096

Length L: 50 mm

Width B: 50 mm

Connection: Bayonet connection

Suct. cups: Bellows suct. cup SPB2



RFBP 100 58 BA SPB2

Part no.:10.01.45.00091

Length L: 100 mm

Width B: 58 mm

Connection: Bayonet connection

Suct. cups: Bellows suct. cup SPB2

Flange extension VEE-FE

VEE-FE 25.4x131.5

Part no...:10.01.36.00109

<https://www.schmalz.com/10.01.36.00109>



RFBP 100 58 BA O10

Part no...:10.01.45.00092

Length L: 100 mm

Width B: 58 mm

Connection: Bayonet connection

Material type: Foam O, Height 10 mm



RFBP 120 120 BA SPB2

Part no...:10.01.45.00085

Length L: 120 mm

Width B: 120 mm

Connection: Bayonet connection

Suct. cups: Bellows suct. cup SPB2



RFBP 120 120 BA O10

Part no...:10.01.45.00086

Length L: 120 mm

Width B: 120 mm

Connection: Bayonet connection

Material type: Foam O, Height 10 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de