

Vacuum pump

EVE-OG 165 AC3 F

Part no...:10.03.02.00049

<https://www.schmalz.com/10.03.02.00049>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Oil-Lubricated Vacuum Pumps EVE-OG > EVE-OG 165 AC3 F

Oil-lubricated pump for maximum vacuum levels, requires little maintenance



Current type: three-phase current

Sound level at 50 Hz: 70 dB(A)

with: Filter


Suction rate (50 Hz): 165 m³/h

Rated power 50 Hz: 4 kW

Voltage at 50Hz: 230/400V AC3

Weight: 140 kg

Design Data



Attribute	Value
B	542 mm
B2	94 mm
G2	G2-1/2-F
G3	G2-F
G5	M10-F
H	418 mm
H1	680 mm
H2	240 mm
L	890 mm
L2	253 mm
X1	243 mm
X2	430 mm
X3	40 mm
Y1	305 mm

Technical Data

Attribute	Value
Max. vacuum	-980 mbar
Max. vacuum	-28.94 inHg
Suction rate (50 Hz)	165 m³/h
Voltage at 50Hz	230/400V AC3

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum pump

EVE-OG 165 AC3 F

Part no.:10.03.02.00049

<https://www.schmalz.com/10.03.02.00049>

Rated power 50 Hz	4 kW
Sound level at 50 Hz	70 dB(A)
Weight	140 kg
Protection type IP	IP 55
Current type	AC3
Product family	EVE-OG

Accessories



DRM 40 P1 H

Part no.:10.07.02.00051

External diameter D: 40 mm

Measuring range: 0,0 ... 1,0 bar

Construction shape manometers: Connection at rear

Thread G1: G1"-M



MSS-K 8-12A

Part no.:10.04.04.00123

Construction use: PKZM0

Protection type IP: IP 65

Measuring range: bar

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum pump

EVE-OG 165 AC3 F

Part no.:10.03.02.00049

<https://www.schmalz.com/10.03.02.00049>



OEL EVE-OG 1L ANDEROL 555

Part no.:27.02.01.00055

Construction use: Pump EVE-OG



OEL EVE-OG 5L ANDEROL 555

Part no.:27.02.01.00056

Construction use: Pump EVE-OG



ZUB EVE-OG Ölablass-Kit

Part no.:22.09.03.00038

Construction use: Pump EVE-OG

Spare parts

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum pump

EVE-OG 165 AC3 F

Part no...:10.03.02.00049

<https://www.schmalz.com/10.03.02.00049>



FILT-EINS 3 150x222 PAP STF-2-1/2-IG

Part no...:10.07.01.00020

Filter pore size: 3 µm

External diameter D: 150 mm

Length L: 222 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 2-1/2-IG



OEL EVE-OG 5L ANDEROL 555

Part no...:27.02.01.00056

Construction use: Pump EVE-OG



VST EVE-OG-165-255

Part no...:10.03.02.00057

Construction use: Pump EVE-OG

Size: 165-255

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de