

Vacuum centre

VZ-OG 165 AC3 200

Part no...:10.03.04.00166

<https://www.schmalz.com/10.03.04.00166>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Centers > Vacuum Centers VZ > VZ-OG 165 AC3 200

Vacuum centre with oil-lubricated pump and vacuum reservoir




Suction rate: 165 m³/h

Voltage: 230/400 V, 50 Hz

Reservoirs volume: 200 l

Design Data



Attribute	Value
B	710 mm
B1	1040 mm
d	11 mm
G2	G2-1/2-F
H	950 mm
L	910 mm
L1	1040 mm
X1	592 mm
Y1	670 mm

Technical Data

Attribute	Value
Max. vacuum	-980 mbar
Voltage	230/400 V, 50 Hz
Motor power	4 kW
Reservoirs volume	200 l
Suction rate	165 m ³ /h
Protection type IP	IP 54
Weight	271 kg
Product family	VZ

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum centre

VZ-OG 165 AC3 200

Part no...:10.03.04.00166

<https://www.schmalz.com/10.03.04.00166>

Accessories



OEL EVE-OG 1L ANDEROL 555

Part no...:27.02.01.00055

Construction use: Pump EVE-OG



OEL EVE-OG 5L ANDEROL 555

Part no...:27.02.01.00056

Construction use: Pump EVE-OG

Spare parts



FILT-EINS 3 150x222 PAP STF-2-1/2-IG

Part no...:10.07.01.00020

Filter pore size: 3 µm

External diameter D: 150 mm

Length L: 222 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 2-1/2-IG

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum centre

VZ-OG 165 AC3 200

Part no...:10.03.04.00166

<https://www.schmalz.com/10.03.04.00166>



OEL-FILT EVE-OG-250

Part no...:10.03.02.00011

Size: 250

Construction use: Pump EVE-OG



VST EVE-OG-165-255

Part no...:10.03.02.00057

Construction use: Pump EVE-OG

Size: 165-255

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de