

Vacuum centre

VZ-OG 100 AC3 100 GMS

Part no.:10.03.04.00122

<https://www.schmalz.com/10.03.04.00122>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Centers > Vacuum Centers VZ > VZ-OG 100 AC3 100 GMS

Vacuum centre with oil-lubricated pump and vacuum reservoir




Suction rate: 100 m³/h

Voltage: 230/400V ±10%

Reservoirs volume: 100 l

with: Regulated engine circuit

Design Data



Attribute	Value
B	610 mm
B1	750 mm
d	11 mm
G2	G1-1/4"-F
H	700 mm
L	710 mm
L1	750 mm
X1	480 mm
Y1	570 mm

Technical Data

Attribute	Value
Max. vacuum	-750 mbar
Voltage	230/400V ±10%
Motor power	2.20 kW
Reservoirs volume	100 l
Suction rate	100 m ³ /h
Protection type IP	IP 44
Weight	131.50 kg
Product family	VZ

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum centre

VZ-OG 100 AC3 100 GMS

Part no...:10.03.04.00122

<https://www.schmalz.com/10.03.04.00122>

Accessories



OEL EVE-OG 1L ANDEROL 555

Part no...:27.02.01.00055

Construction use: Pump EVE-OG

Spare parts



ERS-SET EVE-OG 63+100

Part no...:10.03.02.00012

Size: 63+100

Construction use: Pump EVE-OG



FILT-EINS 3 98x70 PAP STF-1-1/4-IGN

Part no...:10.07.01.00018

Filter pore size: 3 µm

External diameter D: 98 mm

Length L: 70 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 1-1/4-IGN

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum centre

VZ-OG 100 AC3 100 GMS

Part no...:10.03.04.00122

<https://www.schmalz.com/10.03.04.00122>



OEL-FILT EVE-OG-40-100G

Part no...:10.03.02.00009

Size: 40-100G

Construction use: Pump EVE-OG

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de