

Dust filter (with pressure monitor)

STF-D 60 P 4.5 F SSD

Part no.:10.07.01.00266

<https://www.schmalz.com/10.07.01.00266>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Vacuum Filters VF / STF / STF-D > STF-D 60 P 4.5 F SSD

Dust filter (with pressure monitor)



Connection: Ø60mm

Shape: Piclon housing


Nominal flow rate: 270 m³/h

Filter pore size: 3 µm

Add. function: Filter monitoring

Additional function: Hose clamps SSD

Design Data



Attribute	Value
B1	221 mm
B2	112 mm
d	8.50 mm
D	170 mm
D1	198 mm
D2	60 mm
D3	60 mm
H	218 mm
L	355 mm
L1	658 mm
L2	303 mm
X1	192 mm

Technical Data

Attribute	Value
Connection	Ø60mm
Nominal flow rate	270 m³/h
Nominal flow rate	4500 l/min
Max. vacuum	-500 mbar
Filter pore size	3 µm
Weight	2.10 kg

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Dust filter (with pressure monitor)

STF-D 60 P 4.5 F SSD

Part no.:10.07.01.00266

<https://www.schmalz.com/10.07.01.00266>

Product family

VF

Spare parts



FILT-EINS 3 124x320 PAP STF-Picl-4.5

Part no.:10.07.01.00060

Filter pore size: 3 µm


External diameter D: 124 mm

Length L: 320 mm

Filter material: Paper

Construction use: Dust filter STF

Size: Picl-4.5



DDW 10...50 250V-AC/6

Part no.:21.01.06.00011



SSD 60-68 ST-VZ

Part no.:10.07.10.00017

Clamping range: 60.0 ... 68.0 mm

Material: Steel

Surface: galvanised

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Dust filter (with pressure monitor)

STF-D 60 P 4.5 F SSD

Part no.:10.07.01.00266

<https://www.schmalz.com/10.07.01.00266>



FILT-EINS 122x320 PAP STF-Picl-4.5

Part no.:11.04.03.10086

External diameter D: 122 mm

Length L: 320 mm

Filter material: Paper

Construction use: Dust filter STF

Size: Picl-4.5



FILT-EINS 3 124x320 PAP STF-Picl-4.5

Part no.:10.07.01.00060

Filter pore size: 3 µm

External diameter D: 124 mm

Length L: 320 mm

Filter material: Paper

Construction use: Dust filter STF

Size: Picl-4.5