

## Hose clamp

SSD 85-90 ST-VZ

Part no...:10.07.10.00102

<https://www.schmalz.com/10.07.10.00102>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Hose Clamps SSB / SSD > SSD 85-90 ST-VZ

### Hose clamp for securing wire-reinforced hoses




Clamping range: 85.0 ... 90.0 mm

Material: Steel

Surface: galvanised

### Design Data



| Attribute | Value |
|-----------|-------|
| d1        | 85 mm |
| d2        | 90 mm |
| L         | 19 mm |

### Technical Data

| Attribute      | Value            |
|----------------|------------------|
| Clamping range | 85.0 ... 90.0 mm |
| Material       | Steel            |
| Weight         | 46.10 g          |
| Product family | SSB / SSD        |

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Hose clamp

SSD 85-90 ST-VZ

Part no.:10.07.10.00102

<https://www.schmalz.com/10.07.10.00102>

### Accessories



#### VSL 86-75 PU-DS-AS TR

Part no.:10.07.09.00054

External diameter D: 86 mm

Internal diameter d: 75 mm

Length max.: 15 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 66 mm

Pressure range (operating pressure): -0.50 ... 1.69 bar

Operating temperature: -40 ... 90 °C



#### VSL 85-75 PVC-PS GR

Part no.:10.07.09.00048

External diameter D: 85 mm

Internal diameter d: 75 mm

Length max.: 10 m

Material hose: PVC with PVC-spiral

Bending radius min.: 114 mm

Pressure range (operating pressure): -0.29 ... 1.00 bar

Operating temperature: -20 ... 70 °C



#### VSL 87-75 PU-DS-AS

Part no.:10.07.09.00061

External diameter D: 87 mm

Internal diameter d: 75 mm

Length max.: 15 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 195 mm

Pressure range (operating pressure): -1.00 ... 2.36 bar

Operating temperature: -40 ... 90 °C

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)