

Multi-Base

VC-M-BV 265x170x209

Part no...:10.01.12.02050

<https://www.schmalz.com/10.01.12.02050>



Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Manual Work > Multi-Clamp System VC-M / VC-M-V > VC-M-BV 265x170x209

Turning and slewing device Base



Length L: 265 mm
Width B: 170 mm
Height H: 209 mm

Design Data



Attribute	Value
B	170 mm
H	209 mm
L	265 mm

Technical Data

Attribute	Value
Weight	7.34 kg

Accessories

Multi-Base

VC-M-BV 265x170x209

Part no...:10.01.12.02050

<https://www.schmalz.com/10.01.12.02050>



DI-PROF 8x10.5 MOS EPDM-15

Part no...:10.01.12.02056



FU 5 3/2 -

Part no...:10.01.12.02055

Nominal size: 5 mm

Thread G1: G1/4"-F



REIB-INS 8.1x18 VC-M

Part no...:10.01.12.02000

Construction use: Multi-Clamp

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Multi-Base

VC-M-BV 265x170x209

Part no...:10.01.12.02050

<https://www.schmalz.com/10.01.12.02050>



VC-M-PU 4 110V-AC

Part no...:10.01.12.02051

Current type: 1-phase AC 110V

Max. vacuum: -850 mbar

Nominal size: 9 mm



VC-M-PU 4 230V-AC

Part no...:10.01.12.02040

Current type: 1-phase AC 230V

Max. vacuum: -850 mbar

Nominal size: 9 mm



VC-M-SPV 160x160x30

Part no...:10.01.12.01853

Length L: 160 mm

Width B: 160 mm

Height H: 30 mm

Suction rate: 3 m³/h

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Multi-Base

VC-M-BV 265x170x209

Part no...:10.01.12.02050

<https://www.schmalz.com/10.01.12.02050>



VC-M-SPV 200x55

Part no...:10.01.12.02009

Length L: 200 mm

Width B: 55 mm



VC-M-SPV 210

Part no...:10.01.12.02008

External diameter D: 210 mm



VC-M-SPV 300x100

Part no...:10.01.12.02053

Length L: 300 mm

Width B: 100 mm

Contact Schmalz


J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Multi-Base

VC-M-BV 265x170x209

Part no...:10.01.12.02050

<https://www.schmalz.com/10.01.12.02050>



ZUB VC-M-V

Part no...:10.01.12.02054

Construction use: Multi-Clamp

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de