

Vacuum block

VCBL-B 120x50x29 TV

Part no...:10.01.12.03167

<https://www.schmalz.com/10.01.12.03167>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Systems from Biesse > Vacuum Blocks
VCBL-B > VCBL-B 120x50x29 TV

Vacuum block




Dimensions (LxB): 120 x 50

Height H: 29 mm

Add. function: Sensing valve

Design Data



Attribute	Value
B	50 mm
H	29 mm
H2	19 mm
L	120 mm
L1	146 mm

Technical Data

Attribute	Value
Weight	0.32 kg

Biesse is a registered and protected trademark. The articles listed here are products of J. Schmalz GmbH that have been designed to fit CNC machining centers from Biesse.

Accessories

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum block

VCBL-B 120x50x29 TV

Part no...:10.01.12.03167

<https://www.schmalz.com/10.01.12.03167>



SCHE 90/17x0.4 ST VCBL-B

Part no...:10.01.12.03188

External diameter D: 90 mm

Internal diameter d: 17 mm

Height H: 0.4 mm

Length L: 0.4 mm

Material: Steel

Construction use: Vacuum block VCBL-S

Spare parts



ADP-RING-100.5x15.5-VCBL-B

Part no...:10.01.12.03345

External diameter D: 100.5 mm

Height H: 15.5 mm

Construction use: Vacuum block VCBL-S



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum block

VCBL-B 120x50x29 TV

Part no...:10.01.12.03167

<https://www.schmalz.com/10.01.12.03167>



VCSP-O 120x50x15.5 TPE

Part no...:10.01.12.00012

Length L: 120 mm

Width B: 50 mm

Height H: 15.5 mm



ERS VCTV

Part no...:10.01.12.01651

Construction use: Sensing valve vacuum block

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de