

Multi-Clamp - Suction plate

VC-M-SPV 160x160x30

Part no...:10.01.12.01853

<https://www.schmalz.com/10.01.12.01853>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Manual Work > Multi-Clamp Suction Plates VC-M-SP / VC-M-SPV > VC-M-SPV 160x160x30

Multi-Clamp - Suction plate for operation with vacuum pump




Length L: 160 mm

Width B: 160 mm

Height H: 30 mm

Suction rate: 3 m³/h

Design Data



Attribute	Value
B	160 mm
H	30 mm
d	6 mm
L	160 mm

Technical Data

Attribute	Value
Weight	0.90 kg

Accessories

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Multi-Clamp - Suction plate

VC-M-SPV 160x160x30

Part no...:10.01.12.01853

<https://www.schmalz.com/10.01.12.01853>



DI-PROF 8x10.5 MOS EPDM-15

Part no...:10.01.12.02056



FU 5 3/2 -

Part no...:10.01.12.02055

Nominal size: 5 mm

Thread G1: G1/4"-F



REIB-INS 8.1x18 VC-M

Part no...:10.01.12.02000

Construction use: Multi-Clamp

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Multi-Clamp - Suction plate

VC-M-SPV 160x160x30

Part no...:10.01.12.01853

<https://www.schmalz.com/10.01.12.01853>



VC-M-BV 265x170x209

Part no...:10.01.12.02050

Length L: 265 mm

Width B: 170 mm

Height H: 209 mm



VC-M-PU 4 110V-AC

Part no...:10.01.12.02051

Current type: 1-phase AC 110V

Max. vacuum: -850 mbar

Nominal size: 9 mm



VC-M-PU 4 230V-AC

Part no...:10.01.12.02040

Current type: 1-phase AC 230V

Max. vacuum: -850 mbar

Nominal size: 9 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Multi-Clamp - Suction plate

VC-M-SPV 160x160x30

Part no...:10.01.12.01853

<https://www.schmalz.com/10.01.12.01853>



ZUB VC-M-V

Part no...:10.01.12.02054

Construction use: Multi-Clamp

Spare parts



REIB-INS 8.1x18 VC-M

Part no...:10.01.12.02000

Construction use: Multi-Clamp



DI-PROF 8x10.5 MOS EPDM-15

Part no...:10.01.12.02056

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de