

## Vacuum pump

EVE-TR-X 25 AC3 IE3-TYP2 F-VB

Part no.:10.03.01.00355

<https://www.schmalz.com/10.03.01.00355>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Dry-Running Vacuum Pumps EVE-TR X > EVE-TR-X 25 AC3 IE3-TYP2 F-VB

**Oil-free pump with const. suct. rate robust, requ. little maintenance long service life, cont. operation**



Current type: three-phase current

Voltage at 60Hz: YY230/Y460V  $\pm 10\%$

Voltage at 60 Hz opt: D208V  $\pm 10\%$  (o. IE3)

Suction rate (60 Hz): 30 m<sup>3</sup>/h

Vacuum (60 Hz): -900 mbar

Construction: IE3:US/CAN


Rated power 60 Hz: 0.9 kW

Permission: UL/CSA

Weight: 28.5 kg

Permission: UL/CSA

### Design Data



| Attribute | Value   |
|-----------|---------|
| B         | 270 mm  |
| B2        | 50 mm   |
| d         | 7 mm    |
| G2        | G3/4"-F |
| G3        | G3/4"-F |
| H         | 292 mm  |
| H1        | 380 mm  |
| H2        | 70 mm   |
| L         | 495 mm  |
| L2        | 96 mm   |
| X1        | 220 mm  |
| Y1        | 190 mm  |

### Technical Data

| Attribute            | Value                  |
|----------------------|------------------------|
| Suction rate (60 Hz) | 30 m <sup>3</sup> /h   |
| Voltage at 60Hz      | YY230/Y460V $\pm 10\%$ |
| Rated power 60 Hz    | 0.90 kW                |
| Weight               | 28.50 kg               |
| Protection type IP   | IP 55                  |
| Current type         | AC3                    |

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Vacuum pump

EVE-TR-X 25 AC3 IE3-TYP2 F-VB

Part no.:10.03.01.00355

<https://www.schmalz.com/10.03.01.00355>

Product family

EVE-TR-X

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

### Spare parts



#### VST EVE-TR-X-25

Part no.:10.03.01.00225

Construction use: Pump EVE-TR-X

Size: 25

contains: Brush slide/Filter



#### FILT-EINS EVE-TR-X-25/40

Part no.:10.03.01.00230

Construction use: Pump EVE-TR-X

Size: 25/40



#### VST EVE-TR-X-25

Part no.:10.03.01.00225

Construction use: Pump EVE-TR-X

Size: 25

contains: Brush slide/Filter

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)



## Vacuum pump

EVE-TR-X 25 AC3 IE3-TYP2 F-VB

Part no...:10.03.01.00355

<https://www.schmalz.com/10.03.01.00355>

---

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 |  
customercenter@schmalz.de