

Flat suction cup (oval)

SGON 12x4 NBR-CO-55 M5-AG

Part no.:10.01.05.00238

<https://www.schmalz.com/10.01.05.00238>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > Flat Suction Cups SGON > SGON 12x4 NBR-CO-55 M5-AG

Flat suction cup (oval) for long and also curved workpieces



Dimensions (LxB): 12 x 4


Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: M5-M

Design Data



Attribute	Value
Bmax(S)	5 mm
Bs	3.90 mm
dn	1.50 mm
G1	M5-M
H	18 mm
LG1	4.50 mm
Lmax(S)	13 mm
Ls	11.90 mm
SW1	8 mm
Z (Stroke)	0.50 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Technical Data

Attribute	Value
Suction force (-600mbar)	1.80 N
Volume	0.17 cm ³
Curve radius (min) (convex)	3 mm
Hose diameter (rec.) d	2 mm
Dimensions (LxB)	12 x 4
Number of folds	0
Suction cup material	Nitrile rubber NBR-conductive

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (oval)

SGON 12x4 NBR-CO-55 M5-AG

Part no.:10.01.05.00238

<https://www.schmalz.com/10.01.05.00238>

Material hardness [Shore A]	55 Shore A
Weight	2.90 g
Product family	SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N020 M5-AG DN180

Part no.:10.01.01.00312

Thread G1: M5-M
Length L1: 15 mm
Fitting length: 3 mm
Nominal diameter dn: 1.8 mm
Material: Aluminum



SGO 12x4 NBR-CO-55 N020

Part no.:10.01.05.00237

Dimensions (LxB): 12 x 4
Suction cup material: Nitrile rubber NBR-conductive
Material hardness [Shore A]: 55 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de