

Suction plate (round)

SPU 160 SI-60 G1/2-IG TV

Part no...:10.01.01.01154

<https://www.schmalz.com/10.01.01.01154>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Suction Plates SPU > SPU 160 SI-60 G1/2-IG TV

Suction plate (round), universal, for smooth and slightly rough surfaces




Size: 160

Suction cup material: Silicone SI

Material hardness [Shore A]: 60 Shore A

Connection: G1/2"-F

Design Data



Attribute	Value
d	34 mm
d2	113 mm
Dmax(S)	170 mm
Ds	160 mm
G1	G1/2"-F
G2	G1/4"-M
G3	G1/8"-F
H	25 mm
H1	43 mm
L2	36.50 mm
LG1	13.50 mm
LG2	13 mm
LG3	6 mm
Z (Stroke)	7 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	1090 N
Suction force d2	600 N
Volume	142 cm ³

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suction plate (round)

SPU 160 SI-60 G1/2-IG TV

Part no.:10.01.01.01154

<https://www.schmalz.com/10.01.01.01154>

Curve radius (min) (convex)	350 mm
Hose diameter (rec.) d	9 mm
Size	160
Suction cup material	Silicone SI
Material hardness [Shore A]	60 Shore A
Weight	440 g
Number of folds	0
Product family	SPU

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 160

Part no.:10.01.01.12438

Size: 160

Clamping range: 150.0 ... 180.0 mm

Temperature resistance: 80 °C

Spare parts



TV G1/4-AG 13

Part no.:10.05.10.00061

Thread G1: G1/4"-M

Thread G2: G1/8"-F

Spring stroke Z: 13 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suction plate (round)

SPU 160 SI-60 G1/2-IG TV

Part no...:10.01.01.01154

<https://www.schmalz.com/10.01.01.01154>



DR-SPU 160 SI-60

Part no...:10.01.01.01112

Size: 160

Suction cup material: Silicone SI

Material hardness [Shore A]: 60 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de