

Bellows suction cups (round)

FSGA 110 SI-55 G1/2-IG

Part no.:10.01.06.00119

<https://www.schmalz.com/10.01.06.00119>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSGA (1.5 Folds) from Ø 110 mm > FSGA 110 SI-55 G1/2-IG

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 110

Number of folds: 1.5

Suction cup material: Silicone SI


Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA

Nipple material: Aluminum

Connection: G1/2"-F

Design Data



Attribute	Value
dn	13.50 mm
d2	80 mm
Dmax(S)	130 mm
Ds	111 mm
G1	G1/2"-F
H	69.50 mm
LG1	13 mm
Z (Stroke)	29.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	280 N
Pull-off force	570 N
Volume	330 cm ³
Curve radius (min) (convex)	85 mm
Hose diameter (rec.) d	12 mm
Size	110
Nipple family	N 010

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cups (round)

FSGA 110 SI-55 G1/2-IG

Part no.:10.01.06.00119

<https://www.schmalz.com/10.01.06.00119>

Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Weight	358.30 g
Product family	FSGA
Number of folds	1.50

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



FGA 110 SI-55 N010

Part no.:10.01.06.00115

Size: 110

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5

Material characteristics: FDA-compatible



SA-NIP N010 G1/2-IG

Part no.:10.01.01.00796

Thread G1: G1/2"-F

Material: Aluminum

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cups (round)

FSGA 110 SI-55 G1/2-IG

Part no...:10.01.06.00119

<https://www.schmalz.com/10.01.06.00119>



FGA 110 SI-55 N010

Part no...:10.01.06.00115

Size: 110

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5

Material characteristics: FDA-compatible

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de