

Bellows suction cups (round)

FSG 60 VU1-72 G1/4-IG ON

Part no.:10.01.06.00171

<https://www.schmalz.com/10.01.06.00171>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bellows Suction Cups FSG VU1 (2.5 Folds) > FSG 60 VU1-72 G1/4-IG ON

Bellows suction cup (round) for very uneven workpieces



Size: 60

Suction cup material: Vulkollan VU1


Material hardness [Shore A]: 72 Shore A

Nipple material: Aluminum

Connection: G1/4"-F

Number of folds: 2.5

Design Data



Attribute	Value
d2	36 mm
dn	6 mm
Dmax(S)	62.50 mm
Ds	59 mm
G1	G1/4"-F
H	70 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	30 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	61 N
Pull-off force	100 N
Volume	66.76 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	6 mm
Size	60
Nipple family	N 014

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cups (round)

FSG 60 VU1-72 G1/4-IG ON

Part no.:10.01.06.00171

<https://www.schmalz.com/10.01.06.00171>

Suction cup material	Vulkollan VU1
Material hardness [Shore A]	72 Shore A
Weight	47.10 g
Number of folds	2.50
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N014 G1/4-IG DN600

Part no.:10.01.06.00181

Thread G1: G1/4"-F

Fitting length: 15 mm

Material: Aluminum

External diameter D: 16.5 mm

Spanner size SW2: 6 mm



FG 60 VU1-72 N014 ON

Part no.:10.01.06.00208

Size: 60

Suction cup material: Vulkollan VU1

Material hardness [Shore A]: 72 Shore A

Number of folds: 2.5

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cups (round)

FSG 60 VU1-72 G1/4-IG ON

Part no...:10.01.06.00171

<https://www.schmalz.com/10.01.06.00171>



FG 60 VU1-72 N014 ON

Part no...:10.01.06.00208

Size: 60

Suction cup material: Vulkollan VU1

Material hardness [Shore A]: 72 Shore A

Number of folds: 2.5