

Connection (geared)

SXT-CON-GB-MO-1.5IN

Part no.:10.07.13.00117

<https://www.schmalz.com/10.07.13.00117>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Mounting Elements > Tooling System SXT > Connections (Geared) SXT-CON-GB > SXT-CON-GB-MO-1.5IN

Gear bracket for tube, modular, for swivel arms and to connect with Round Tooling




Material: Aluminum

Connection 1: 1.5 Inch

Shape: Male openable

Design Data



Attribute	Value
B	35 mm
D	35 mm
d	38,10 mm
d1	8,50 mm
H	69,50 mm
H2	26 mm
L	68,50 mm
L2	36,50 mm

Technical Data

Attribute	Value
Material	Aluminum
Shape	Male openable
Weight	205 g
Product family	SXT

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Connection (geared)

SXT-CON-GB-MO-1.5IN

Part no.:10.07.13.00117

<https://www.schmalz.com/10.07.13.00117>

Accessories



SXT-CON-GB-F-D25

Part no.:10.07.13.00114

Material: Aluminum

Connection 1: D25

Shape: Female



SXT-CON-GB-F-D40

Part no.:10.07.13.00115

Material: Aluminum

Connection 1: D40

Shape: Female



SXT-CON-GB-F-1IN

Part no.:10.07.13.00191

Material: Aluminum

Connection 1: 1 Inch

Shape: Female

Connection (geared)

SXT-CON-GB-MO-1.5IN

Part no...:10.07.13.00117

<https://www.schmalz.com/10.07.13.00117>



SXT-EXT-GB2-50

Part no...:10.07.13.00034

External diameter D: 25 mm

Length L: 50,8 mm

Material: Aluminum

Shape: Gear Bracket both sides



SXT-ANG-GB2-F

Part no...:10.07.13.00121

Material: Aluminum

Shape: Female

Shape: Gear Bracket both sides



SET SCHRAUBE FED-SCHE M8x65

Part no...:10.07.13.00178

Thread G: M8

Length L: 65 mm

Connection (geared)

SXT-CON-GB-MO-1.5IN

Part no...:10.07.13.00117

<https://www.schmalz.com/10.07.13.00117>



SET SCHRAUBE FED-SCHE M8x70

Part no...:10.07.13.00179

Thread G: M8

Length L: 70 mm



SET SCHRAUBE FED-SCHE M8x90

Part no...:10.07.13.00182

Thread G: M8

Length L: 90 mm



SET SCHRAUBE FED-SCHE M8x100

Part no...:10.07.13.00183

Thread G: M8

Length L: 100 mm