

Suction cup connection nipple

SA-NIP N005 G1/8-IG DN200

Osanro.:10.01.01.03521

<https://www.schmalz.com/10.01.01.03521>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Litteä imukuppi (pyöreä) > SA-NIP N005 G1/8-IG DN200

Suction cup connection nipple



Nipple family: N 005

Thread G1: G1/8"-F

Length L1: 20,5 mm


Length L: 16 mm

Fitting length: 16 mm

Nominal diameter dn: 2 mm

Material: Aluminum

Suunnitteludata



Attribuutti	Arvo
dn	2 mm
D	8 mm
D2	5 mm
G1	G1/8"-F
L	16 mm
L1	20,50 mm
L2	2,50 mm
L3	2 mm
LG1	9 mm
SW1	14 mm

Tekniset tiedot

Attribuutti	Arvo
Nipple family	N 005
Material	Aluminum
Weight	5,30 g

Lisätarvikkeet

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Suction cup connection nipple

SA-NIP N005 G1/8-IG DN200

Osanro.:10.01.01.03521

<https://www.schmalz.com/10.01.01.03521>



PFG 15 FPM-65 N005

Osanro.:10.01.01.00071

Size: 15

Suction cup material: Fluorocautchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking



PFG 15 HT1-60 N005

Osanro.:10.01.01.11162

Size: 15

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking



PFG 15 NBR-CO-55 N005

Osanro.:10.01.01.10067

Size: 15

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Suction cup connection nipple

SA-NIP N005 G1/8-IG DN200

Osanro.:10.01.01.03521

<https://www.schmalz.com/10.01.01.03521>



PFG 15 NBR-55 N005

Osanro.:10.01.01.00011

Size: 15

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A



PFG 15 PU-55 N005

Osanro.:10.01.01.00051

Size: 15

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A



PFG 15 SI-CO-55 N005

Osanro.:10.01.01.00627

Size: 15

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

Suction cup connection nipple

SA-NIP N005 G1/8-IG DN200

Osanro.:10.01.01.03521

<https://www.schmalz.com/10.01.01.03521>



PFG 15 SI-55 N005

Osanro.:10.01.01.00031

Size: 15

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible