

Vacuum hose (meter)

VSL 49-38 PU-DS-AS TR

부품 번호...10.07.09.00052

<https://www.schmalz.com/10.07.09.00052>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 필터 및 연결부품 > 호스 및 커넥터 > VSL 진공 / 압축 공기 호스 > VSL 49-38 PU-DS-AS TR

Hose for vacuum and compressed-air systems



External diameter D: 49 mm

Internal diameter d: 38 mm

Length max.: 15 m


Material hose: PU, wire spiral, antistatic

Bending radius min.: 104 mm

Pressure range (operating pressure): -1.00 ... 4.47 bar

Operating temperature: -20 ... 90 °C

디자인 데이터



속성

값

d 38 mm

D 49 mm

기술 데이터

속성	값
Hose type	49-38
Pressure range (operating pressure)	-1.00 ... 4.47 bar
Operating temperature	-20 ... 90 °C
Bending radius min.	104 mm
Length max.	15 m
Weight/Meter	790 g/m
Weight/Meter	0.79 kg/m
Material hose	PU, wire spiral, antistatic

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8402403 | ...에서 3
schmalz@schmalz.co.kr

Vacuum hose (meter)

VSL 49-38 PU-DS-AS TR

부품 번호...10.07.09.00052

<https://www.schmalz.com/10.07.09.00052>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

부속품



SSD 43-48 ST-VZ

부품 번호...10.07.10.00020

Clamping range: 43.0 ... 48.0 mm

Material: Steel

Surface: galvanised



SSD 45-50 ST-VZ

부품 번호...10.07.10.00157

Clamping range: 45.0 ... 50.0 mm

Material: Steel

Surface: galvanised



ST G1-1/2-AG 38 MS-V

부품 번호...10.08.03.00170

Thread G1: G1-1/2"-M

Hose diameter (rec.) d: 38 mm

Material: Brass

Surface: nickel plated

Length L: 12.2 mm

Nominal diameter dn: 29.9 mm

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462402 |...에서 3
schmalz@schmalz.co.kr



Vacuum hose (meter)

VSL 49-38 PU-DS-AS TR

부품 번호...10.07.09.00052

<https://www.schmalz.com/10.07.09.00052>

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 | ...에서 3
schmalz@schmalz.co.kr