

Bellows suction cup (round)

FGA 33 HT1-60 N018

부품 번호...10.01.06.00873

<https://www.schmalz.com/10.01.06.00873>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 주름 진공 패드 (원형) > FGA 33 HT1-60 N018

Bellows suction cup (round) with optimal adaptation to uneven surfaces




Size: 33

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 1.5

디자인 데이터



속성

값

d 8 mm

d1 16 mm

d2 17 mm

D1 36 mm

Dk 18 mm

Dmax(S) 38 mm

Ds 30 mm

H 27 mm

H2 13 mm

H3 14 mm

Z (Stroke) 9 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Number of folds	1.50
Suction force (-600mbar)	13.60 N
Size	33
Suction cup material	High temperature material HT1
Weight	6.80 g
Curve radius (min) (convex)	40 mm

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8402403 | ...에서 3
schmalz@schmalz.co.kr

Bellows suction cup (round)

FGA 33 HT1-60 N018

부품 번호...10.01.06.00873

<https://www.schmalz.com/10.01.06.00873>

Product family

FGA

부속품



SA-NIP N018 G1/4-AG DN440

부품 번호...10.01.06.01065

Nipple family: N 018

Thread G1: G1/4"-M

Length L1: 28.8 mm

Fitting length: 4 mm

Nominal diameter dn: 4.4 mm

Spanner size SW2: 5 mm

Material: Aluminum



SA-NIP N018 G1/4-IG DN440

부품 번호...10.01.06.01066

Nipple family: N 018

Thread G1: G1/4"-F

Length L1: 28.8 mm

Fitting length: 15 mm

Nominal diameter dn: 4.4 mm

Spanner size SW2: 5 mm

Material: Aluminum



SPI 32 PEEK

부품 번호...10.01.06.03287

Size: 32

Material: Polyetheretherketon



Bellows suction cup (round)

FGA 33 HT1-60 N018

부품 번호...10.01.06.00873

<https://www.schmalz.com/10.01.06.00873>

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 | ...에서 3
schmalz@schmalz.co.kr