

Suction plate (round)

SPK 250 MOS EPDM-15 G1/2-IG

부품 번호...10.01.01.12065

<https://www.schmalz.com/10.01.01.12065>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 평면 진공 패드 (원형) > Suction Plates SPK > SPK 250 MOS EPDM-15 G1/2-IG

Suction plate (round) for rough and structured surfaces



Size: 250


Material hardness [Shore A]: 15 Shore A

Material type: Foam rubber

Sealing material: EPDM

Connection: G1/2"-F

디자인 데이터



속성

값

d3 235 mm

Dmax(S) 269 mm

Ds 249 mm

G1 G1/2"-F

G2 G1/2"-F

H 25.50 mm

L2 76 mm

LG1 14.50 mm

LG2 14.50 mm

Z (Stroke) 6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Suction force (-600mbar)	2714 N
Volume	291 cm ³
Curve radius (min) (convex)	2600 mm
Hose diameter (rec.) d	12 mm
Size	250
Material hardness [Shore A]	15 Shore A
Weight	2310 g

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 |...에서 3
schmalz@schmalz.co.kr

Suction plate (round)

SPK 250 MOS EPDM-15 G1/2-IG

부품 번호...:10.01.01.12065

<https://www.schmalz.com/10.01.01.12065>

Number of folds	0
Product family	SPK

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

부속품



TV G1/2-AG 13

부품 번호...:10.05.10.00038

Thread G1: G1/2"-M

Thread G2: G3/8"-F

Spring stroke Z: 13 mm



SU 280

부품 번호...:10.01.01.12485

Size: 280

Clamping range: 270.0 ... 300.0 mm

Temperature resistance: 80 °C

예비 부품

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462402 |...에서 3
schmalz@schmalz.co.kr

Suction plate (round)

SPK 250 MOS EPDM-15 G1/2-IG

부품 번호...10.01.01.12065

<https://www.schmalz.com/10.01.01.12065>



DR-SPK 250 MOS EPDM-15

부품 번호...10.01.01.12077

Size: 250

Material type: Foam rubber

Material hardness [Shore A]: 15 Shore A

Sealing material: EPDM



VRS-S G1/4-AG

부품 번호...10.08.06.00048

Thread G1: G1/4"-M

Material: Brass

Surface: nickel plated



DR-SPK 250 MOS EPDM-15

부품 번호...10.01.01.12077

Size: 250

Material type: Foam rubber

Material hardness [Shore A]: 15 Shore A

Sealing material: EPDM