

Bellows suction cups (round)

FSGA 60 VU1-72 G1/4-IG

Part no.:10.01.06.00240

<https://www.schmalz.com/10.01.06.00240>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bellows Suction Cups FSGA VU1 (1.5 Folds) > FSGA 60 VU1-72 G1/4-IG

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 60

Suction cup material: Vulkollan VU1


Material hardness [Shore A]: 72 Shore A

Nipple material: Aluminum

Connection: G1/4"-F

Number of folds: 1,5

Design Data



Attribute	Value
d2	41 mm
dn	6 mm
Dmax(S)	61,50 mm
Ds	59 mm
G1	G1/4"-F
H	49 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	12,50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	75 N
Pull-off force	120 N
Volume	31 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	6 mm
Size	60
Nipple family	N 014

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cups (round)

FSGA 60 VU1-72 G1/4-IG

Part no.:10.01.06.00240

<https://www.schmalz.com/10.01.06.00240>

Suction cup material	Vulkollan VU1
Material hardness [Shore A]	72 Shore A
Weight	38,20 g
Product family	FSGA
Number of folds	1,50

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N014 G1/4-IG DN600

Part no.:10.01.06.00181

Thread G1: G1/4"-F
Fitting length: 15 mm
Material: Aluminum
External diameter D: 16,5 mm
Spanner size SW2: 6 mm



FGA 60 VU1-72 N014

Part no.:10.01.06.00178

Size: 60
Suction cup material: Vulkollan VU1
Material hardness [Shore A]: 72 Shore A
Number of folds: 1,5

Bellows suction cups (round)

FSGA 60 VU1-72 G1/4-IG

Part no...:10.01.06.00240

<https://www.schmalz.com/10.01.06.00240>



FGA 60 VU1-72 N014

Part no...:10.01.06.00178

Size: 60

Suction cup material: Vulkollan VU1

Material hardness [Shore A]: 72 Shore A

Number of folds: 1,5