

Robots-Set ECBPi

ROB-SET ECBPi OMRON

Onderdeelnr...:10.03.01.00544

<https://www.schmalz.com/10.03.01.00544>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Vacuümgenerator > Vacuümgenerator einde van de arm > Handling Sets ECBPi > ROB-SET ECBPi OMRON

Complete set voor het aansluiten en integreren van de CobotPump ECBPi op lichtgewicht robots




Construction use: CobotPump

for: OMRON

Type: TM5, TM12, TM14

Ontwerpgegevens



Attribuut	Waarde
H	202,60 mm
D	151,50 mm

Technische gegevens

Attribuut	Waarde
Suction rate (max.)	12 l/min
Operating temperature	0 ... 45 °C
for	OMRON
Product family	ROB-SET-ECBPI

The technical properties of the robot types may vary by region. The stated compatibility of the set is based on standard European models.

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Robots-Set ECBPi

ROB-SET ECBPi OMRON

Onderdeelnr...:10.03.01.00544

<https://www.schmalz.com/10.03.01.00544>

Accessoires



VEE 2xSPB1/SPF 154.3x42.3

Onderdeelnr...:10.01.36.00268

Number of cups: 2

Suct. cups: Zuignap SPB1/SPF

Length L: 154,3 mm

Width B: 42,3 mm



VEE 4xSPB1/SPF 218.3

Onderdeelnr...:10.01.36.00269

Number of cups: 4

Suct. cups: Zuignap SPB1/SPF

Length L: 218,3 mm



VEE SET-ECBPi

Onderdeelnr...:10.01.36.00266

Robots-Set ECBPi

ROB-SET ECBPi OMRON

Onderdeelnr...:10.03.01.00544

<https://www.schmalz.com/10.03.01.00544>



RFBP 50 50 BA SPB2

Onderdeelnr...:10.01.45.00096

Length L: 50 mm

Width B: 50 mm

Connection: Verbind v de bajonet

Suct. cups: Balg-zuignap SPB2



RFBP 100 58 BA SPB2

Onderdeelnr...:10.01.45.00091

Length L: 100 mm

Width B: 58 mm

Connection: Verbind v de bajonet

Suct. cups: Balg-zuignap SPB2



RFBP 100 58 BA O10

Onderdeelnr...:10.01.45.00092

Length L: 100 mm

Width B: 58 mm

Connection: Verbind v de bajonet

Material type: Schuim O, Hoogte 10 mm

Robots-Set ECBPi

ROB-SET ECBPi OMRON

Onderdeelnr...:10.03.01.00544

<https://www.schmalz.com/10.03.01.00544>



RFBP 120 120 BA SPB2

Onderdeelnr...:10.01.45.00085

Length L: 120 mm

Width B: 120 mm

Connection: Verbind v de bajonet

Suct. cups: Balg-zuignap SPB2



RFBP 120 120 BA O10

Onderdeelnr...:10.01.45.00086

Length L: 120 mm

Width B: 120 mm

Connection: Verbind v de bajonet

Material type: Schuim O, Hoogte 10 mm

Onderdelen



SPF 40 ED-65 G1/4-AG

Onderdeelnr...:10.01.01.13246

Size: 40

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/4"-M

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Robots-Set ECBPi

ROB-SET ECBPi OMRON

Onderdeelnr...:10.03.01.00544

<https://www.schmalz.com/10.03.01.00544>



SPB1 40 ED-65 G1/4-AG

Onderdeelnr...:10.01.06.03498

Size: 40

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/4"-M

Number of folds: 1,5