

Bellows suction cup (round)

FGA 19 PVC-50 N056

Część nr.: 10.01.06.01975

<https://www.schmalz.com/10.01.06.01975>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki do opakowań > Bellows Suction Cups FGA PVC (1.5 Folds) > FGA 19 PVC-50 N056

Przyssawka mieszkowa (okrągła)




Size: 19

Suction cup material: Polyvinyl chloride PVC

Material hardness [Shore A]: 50 Shore A

Number of folds: 1,5

Dane projektowe



Atrybut	Wartość
d	6,60 mm
d2	12,20 mm
D1	19 mm
Dk	13 mm
Dmax(S)	21,50 mm
Ds	19 mm
H	18,70 mm
H2	8,20 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Dane techniczne

Atrybut	Wartość
Suction force (-600mbar)	5,90 N
Pull-off force	10 N
Volume	2,02 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	4 mm
Size	19
Nipple family	N 056

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bellows suction cup (round)

FGA 19 PVC-50 N056

Część nr.:10.01.06.01975

<https://www.schmalz.com/10.01.06.01975>

Number of folds	1,50
Suction cup material	Polyvinyl chloride PVC
Material hardness [Shore A]	50 Shore A
Weight	1,50 g
Product family	FGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Akcesoria



SA-NIP N056 M5-AG DN200

Część nr.:10.01.06.03080

Nipple: N 056
Thread G1: M5-M
Length L1: 17 mm
Fitting length: 5 mm
Nominal size: 200
Material: Aluminum
Spanner size SW2: 4 mm



SA-NIP N056 G1/8-AG DN400

Część nr.:10.01.06.03571

Nipple: N 056
Thread G1: G1/8"-M
Length L1: 20 mm
Fitting length: 5 mm
Nominal size: 400
Material: Aluminum
Spanner size SW2: 4 mm

Bellows suction cup (round)

FGA 19 PVC-50 N056

Część nr...:10.01.06.01975

<https://www.schmalz.com/10.01.06.01975>



SA-NIP N056 G1/8-IG DN400

Część nr...:10.01.06.03572

Nipple: N 056

Thread G1: G1/8"-F

Length L1: 17 mm

Fitting length: 10 mm

Nominal size: 400

Material: Aluminum

Spanner size SW2: 4 mm