

Bellows suction cup (round)

SPB4 40 SI-55 G1/4-AG

부품 번호...10.01.06.03526

<https://www.schmalz.com/10.01.06.03526>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 광영역 그리핑 시스템 및 엔드 이펙터 > 진공 엔드 이펙터 VEE > 진공 엔드 이펙터용 석션 패드 > SPB4 40 SI-55 G1/4-AG

Bellows suction cup (round) for very uneven workpieces



Size: 40


Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Thread G1: G1/4"-M

Number of folds: 4.5

디자인 데이터



속성

값

d2 23 mm

dn 8 mm

Dmax(S) 41.50 mm

Ds 40.50 mm

G1 G1/4"-M

H 73.10 mm

LG1 10 mm

SW1 27 mm

Z (Stroke) 27 mm

기술 데이터

속성	값
Suction force (-600mbar)	25 N
Pull-off force	39 N
Volume	35.74 cm ³
Hose diameter (rec.) d	12 mm
Number of folds	4.50
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Size	40

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 |...에서 3
schmalz@schmalz.co.kr

Bellows suction cup (round)

SPB4 40 SI-55 G1/4-AG

부품 번호...10.01.06.03526

<https://www.schmalz.com/10.01.06.03526>

Weight	40.70 g
Product family	SPB4

부속품



SIEB 19.5x1 MS-A2 103

부품 번호...10.07.01.00321

External diameter D: 19.5 mm

Length L: 1 mm

Material: Brass / Stainless steel

Filter pore size: 103 µm



SSB 20-32 ST-VZ

부품 번호...10.07.10.00003

Clamping range: 20.0 ... 32.0 mm

Material: Steel

Surface: galvanised



SPI 32 PE SPB4-40

부품 번호...10.01.06.02856

Size: 32

Material: Polyethylene

Use: SPB4-40

Bellows suction cup (round)

SPB4 40 SI-55 G1/4-AG

부품 번호...10.01.06.03526

<https://www.schmalz.com/10.01.06.03526>



SPSE 40

부품 번호...10.01.06.02954

Size: 40

예비 부품



SC 090 G1/4-AG

부품 번호...10.01.06.02793

Connection geometry: 090

Vacuum connection: G1/4"-M

Length L1: 33.5 mm

Fitting length: 7.5 mm

Nominal diameter dn: 8 mm



SPB4 40 SI-55 SC090

부품 번호...10.01.06.02590

Size: 40

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 4.5