

Schmalz X-Pump

SXMPi 25 NO Q PC M12-5

부품 번호...10.02.02.05287

<https://www.schmalz.com/10.02.02.05287>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공 발생기 > 콤팩트 이젝터 > Compact Ejectors SXMPi Class B > SXMPi 25 NO Q PC M12-5

Compact ejector with Condition Monitoring, power blow-off function and pneu. air-saving function



Nozzle diameter: 2.5 mm

Electrical connection: Male connect M12, 5 pol

Suction rate (max.): 185 l/min

Air consumption suction: 290 l/min

Pressure range (operating pressure): 3.0 ... 6.0 bar

Max. vacuum: -850 mbar

Control valve: Normally open


Function: Pressure Control

Protection type IP: IP 65

Sound level free: 67 dB(A)

Communication: IO-Link (Class B)

디자인 데이터



속성

값

B	39 mm
d	5.50 mm
G2	M12x1-M
H	108 mm
H1	146 mm
H2	54 mm
H3	6 mm
H4	26 mm
L	210 mm
L2	5 mm
L3	97 mm
X1	89 mm
Y1	10 mm

기술 데이터

속성

값

Nozzle diameter	2.50 mm
-----------------	---------

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 |...에서 3
schmalz@schmalz.co.kr

Schmalz X-Pump

SXMPi 25 NO Q PC M12-5

부품 번호...10.02.02.05287

<https://www.schmalz.com/10.02.02.05287>

Degree of evacuation	85 %
Suction rate (max.)	185 l/min
Suction rate (max.)	11.10 m³/h
Suction rate (max.)	6.533 cfm
Air consumption suction	290 l/min
Air consumption suction	10.241 cfm
Air consumption suction	17.40 m³/h
Sound level free	67 dB(A)
Pressure range (operating pressure)	3.0 ... 6.0 bar
Pressure range (operating pressure)	43.5 ... 87.0
Max. air consumption blow off	320 l/min
Air consumption blow off	11.30 cfm
Air consumption blow off	19.20 m³/h
Recomm. internal hose diameter compressed air	8 mm
Recomm. internal hose diameter vacuum	9 mm
Control valve	Normally open
Weight	0.96 kg
Operating temperature	0 ... 50 °C
Product family	SXMPi

부속품



ASK B-M12-5 5000 S-M12-5

부품 번호...21.04.05.00266

Cable length: 5,000 mm

Material hose: PUR cable

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462402 | ...에서 3
schmalz@schmalz.co.kr

Schmalz X-Pump

SXMPi 25 NO Q PC M12-5

부품 번호...10.02.02.05287

<https://www.schmalz.com/10.02.02.05287>



ASK B-M12-5 2000 S-M12-5

부품 번호...21.04.05.00211

Pressure range (operating pressure): bar

Electrical connection: Fem connect M12, 5 pol

Cable length: 2,000 mm

Material hose: PUR cable



ASK B-M12-5 5000 K-5P

부품 번호...21.04.05.00080

Electrical connection: Fem connect M12, 5 pol

Cable length: 5,000 mm

Material hose: PUR cable