

Balg-zuignap (rond)

FGA 19 PVC-50 N056

Onderdeelnr...:10.01.06.01975

<https://www.schmalz.com/10.01.06.01975>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Vacuümzuignappen > Zuignappen voor de verpakkingindustrie > Bellows Suction Cups FGA PVC (1.5 Folds) > FGA 19 PVC-50 N056

Balgzuiger (rond) met optimale aanpassing aan oneffen oppervlakken




Size: 19

Suction cup material: Polyvinyl chloride PVC

Material hardness [Shore A]: 50 Shore A

Number of folds: 1,5

Ontwerpgegevens



Attribuut	Waarde
d	6,60 mm
d2	12,20 mm
D1	19 mm
Dk	13 mm
Dmax(S)	21,50 mm
Ds	19 mm
H	18,70 mm
H2	8,20 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technische gegevens

Attribuut	Waarde
Suction force (-600mbar)	5,90 N
Pull-off force	10 N
Volume	2,02 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	4 mm
Size	19
Nipple family	N 056

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Balg-zuignap (rond)

FGA 19 PVC-50 N056

Onderdeelnr...:10.01.06.01975

<https://www.schmalz.com/10.01.06.01975>

Number of folds	1,50
Suction cup material	Polyvinyl chloride PVC
Material hardness [Shore A]	50 Shore A
Weight	1,50 g
Product family	FGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessoires



SA-NIP N056 M5-AG DN200

Onderdeelnr...:10.01.06.03080

Nipple: N 056
Thread G1: M5-M
Length L1: 17 mm
Fitting length: 5 mm
Nominal size: 200
Material: Aluminum
Spanner size SW2: 4 mm



SA-NIP N056 G1/8-AG DN400

Onderdeelnr...:10.01.06.03571

Nipple: N 056
Thread G1: G1/8"-M
Length L1: 20 mm
Fitting length: 5 mm
Nominal size: 400
Material: Aluminum
Spanner size SW2: 4 mm

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Balg-zuignap (rond)

FGA 19 PVC-50 N056

Onderdeelnr...:10.01.06.01975

<https://www.schmalz.com/10.01.06.01975>



SA-NIP N056 G1/8-IG DN400

Onderdeelnr...:10.01.06.03572

Nipple: N 056

Thread G1: G1/8"-F

Length L1: 17 mm

Fitting length: 10 mm

Nominal size: 400

Material: Aluminum

Spanner size SW2: 4 mm