

Vacuum pump

EVE-TR-X 80 AC3 IE3-TYP3 F

Part no.:10.03.01.00422

<https://www.schmalz.com/10.03.01.00422>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Generators > Vacuum Pumps > Dry-Running Vacuum Pumps EVE-TR X > EVE-TR-X 80 AC3 IE3-TYP3 F

Oil-free pump with const. suct. rate robust, requ. little maintenance long service life, cont. operation



Current type: three-phase current

Voltage at 50Hz: D200/Y350V $\pm 10\%$ (o. IE3)

Voltage at 60Hz: D220V/Y380-400V $\pm 10\%$

Voltage at 60 Hz opt: D200/Y350V $\pm 10\%$ (o. IE3)

Suction rate (50 Hz): 67 m³/h

Suction rate (60 Hz): 78,5 m³/h

Sound level at 50 Hz: 72 dB(A)

Vacuum (50 Hz): -900 mbar

Vacuum (60 Hz): -900 mbar

Construction: IE3:JPN/KOR/BRA

with: Filter

Rated power 50 Hz: 2,2 kW


Rated power 60 Hz: 2,6 kW

Permission: UL/CSA

Weight: 87,5 kg

Permission: UL/CSA

Design Data



Attribute	Value
B	353 mm
B2	46 mm
d	12 mm
G2	G1-1/4"-F
G3	G1"-F
G5	M8-F
H	328 mm
H1	412,40 mm
H2	75 mm
L	747 mm
L1	768,70 mm
L2	96 mm
X1	326 mm
Y1	190 mm
Y2	95 mm

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Vacuum pump

EVE-TR-X 80 AC3 IE3-TYP3 F

Part no...:10.03.01.00422

<https://www.schmalz.com/10.03.01.00422>

Technical Data

Attribute	Value
Suction rate (50 Hz)	67 m³/h
Suction rate (60 Hz)	78,50 m³/h
Voltage at 50Hz	D200/Y350V ±10% (o. IE3)
Voltage at 60Hz	
Rated power 50 Hz	2,20 kW
Rated power 60 Hz	2,60 kW
Sound level at 50 Hz	72 dB(A)
Weight	87,50 kg
Protection type IP	IP 55
Current type	AC3
Product family	EVE-TR-X

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Spare parts



VST EVE-TR-X-80

Part no...:10.03.01.00227

Construction use: Pump EVE-TR-X

Size: 80

contains: Brush slide/Filter

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Vacuum pump

EVE-TR-X 80 AC3 IE3-TYP3 F

Part no...:10.03.01.00422

<https://www.schmalz.com/10.03.01.00422>



FILT-EINS EVE-TR-X-80/100/140

Part no...:10.03.01.00231

Construction use: Pump EVE-TR-X

Size: 80/100/140



FILT-EINS EVE-TR-X-80

Part no...:10.03.01.00232

Construction use: Pump EVE-TR-X

Size: 80



VST EVE-TR-X-80

Part no...:10.03.01.00227

Construction use: Pump EVE-TR-X

Size: 80

contains: Brush slide/Filter