

Flexolink

FLK G1/4-IG M10x1.25-AG

Číslo dílu...:10.01.03.00206

<https://www.schmalz.com/10.01.03.00206>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Mounting Elements > Jointed Mountings > Flexolink FLK > FLK G1/4-IG M10x1.25-AG

Flexible suction cup mounting for adaptation to sloping surfaces




Thread G1: G1/4"-F

Thread G2: M10x1.25-M

Operating temperature: 0 ... 70 °C

Údaje o konstrukci



Atribut	Wert
dn	2,80 mm
G1	G1/4"-F
G2	M10x1.25-M
L	32 mm
LG1	10,50 mm
LG2	8 mm
SW1	17 mm
W	12 °

Technické údaje

Atribut	Wert
Bending moment	8 Nm
Vertical load	500 N
Weight	26 g
Product family	FLK

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Stránka 1 z 1