

Vacuum pump

EVE-TR 16 AC F

Číslo dílu...:10.03.01.00146

<https://www.schmalz.com/10.03.01.00146>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Generators > Vacuum Pumps > Dry-Running Vacuum Pumps EVE-TR > EVE-TR 16 AC F

Oil-free pump with constant suction rate, robust, requires little maintenance



Current type: 1-phase AC

Sound level at 50 Hz: 61 dB(A)

Voltage at 50Hz: 220-240V

Voltage at 60Hz: 220-240V

Suction rate (50 Hz): 16 m³/h

Suction rate (60 Hz): 19 m³/h

Vacuum (50 Hz): -850 mbar

Rated power 50 Hz: 0,55 kW


Rated power 60 Hz: 0,66 kW

with: Filter

Permission: UL

Weight: 23,4 kg

Údaje o konstrukci



Atribut	Wert
B	231 mm
B2	66 mm
d	7 mm
G2	G3/4-F
G3	G1/2-F
H	214 mm
H1	345 mm
H2	70 mm
L	452 mm
L2	73 mm
X1	202 mm
Y1	125 mm

Technické údaje

Atribut	Wert
Suction rate (50 Hz)	16 m ³ /h
Suction rate (60 Hz)	19 m ³ /h
Voltage at 50Hz	220-240V
Voltage at 60Hz	

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Vacuum pump

EVE-TR 16 AC F

Číslo dílu...:10.03.01.00146

<https://www.schmalz.com/10.03.01.00146>

Rated power 50 Hz	0,55 kW
Rated power 60 Hz	0,66 kW
Current type	AC
Current type	1-phase AC
Sound level at 50 Hz	61 dB(A)
Weight	23,40 kg
Protection type IP	IP 54
Product family	EVE-TR

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Příslušenství



VBV -950...0 G1-AG EVE 10-40

Číslo dílu...:10.03.01.00136

External diameter D: 46 mm

Max. vacuum: -950 mbar

Thread G1: G1"-M

Length L: 53,5 mm

Construction use: Pump EVE

Size: 10-40



MSS-K 4-6.3A

Číslo dílu...:10.04.04.00121

Construction use: PKZM0

Protection type IP: IP 65

Measuring range: bar

Náhradní díly

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Vacuum pump

EVE-TR 16 AC F

Číslo dílu...:10.03.01.00146

<https://www.schmalz.com/10.03.01.00146>



FILT-EINS 3 65x70 PAP STF-3/4-IG

Číslo dílu...:10.07.01.00017

Filter pore size: 3 µm


External diameter D: 65 mm

Length L: 69,5 mm

Filter material: Paper

Construction use: Filters STF

Size: 3/4-IG



VST EVE-TR-16

Číslo dílu...:10.03.01.00133

Construction use: Pump EVE-TR

Size: 16

contains: Brush slide

and: Filter



FILT-EINS EVE-16-25

Číslo dílu...:10.03.01.00022

Size: 16-25

Construction use: Pump EVE