

Flat suction cup (round)

PFG 95 SI-55 N009 M10x1.25-IG

Part no.:10.01.01.00040

<https://www.schmalz.com/10.01.01.00040>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 95 SI-55 N009 M10x1.25-IG

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 95

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Design Data



Attribute	Value
Dk	68.20 mm
Dmax(S)	102 mm
Ds	95 mm
H	21.50 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	350 N
Volume	37.09 cm ³
Curve radius (min) (convex)	200 mm
Size	95
Nipple family	N 009
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Flat suction cup (round)

PFG 95 SI-55 N009 M10x1.25-IG

Part no.:10.01.01.00040

<https://www.schmalz.com/10.01.01.00040>

Weight	87.20 g
Product family	PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N009 G1/4-AG

Part no.:10.01.01.10097

Thread G1: G1/4"-M

Length L1: 25 mm

Material: Aluminum



SA-NIP N009 G1/4-IG

Part no.:10.01.01.10096

Thread G1: G1/4"-F

Length L1: 33 mm

Material: Aluminum

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Flat suction cup (round)

PFG 95 SI-55 N009 M10x1.25-IG

Part no...:10.01.01.00040

<https://www.schmalz.com/10.01.01.00040>



SU 100

Part no...:10.01.01.12840

Size: 100

Clamping range: 100.0 ... 115.0 mm

Temperature resistance: 80 °C