

Flat suction cup (round)

SAF 40 NBR-60 RA

Part no.:10.01.01.10793

<https://www.schmalz.com/10.01.01.10793>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Flat Suction Cups SAF > SAF 40 NBR-60 RA

Flat suction cup (round) for very dynamic handling of smooth and oily workpieces



Size: 40


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: RA

Design Data



Attribute	Value
dn	4 mm
Dmax(S)	46 mm
Ds	41 mm
H	25 mm
L4	31.80 mm
SW1	17 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	69 N
Lateral force	52 N
Lateral force (oily surface)	50 N
Volume	5.30 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	4 mm
Size	40

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Flat suction cup (round)

SAF 40 NBR-60 RA

Part no.:10.01.01.10793

<https://www.schmalz.com/10.01.01.10793>

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A
Weight	27.30 g
Number of folds	0
Product family	SAF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 40

Part no.:10.01.01.12856

Size: 40

Clamping range: 35.0 ... 45.0 mm

Temperature resistance: 80 °C