

Bellows suction cup (oval)

SAOB 140x70 NBR-60 G1/4-IG

Part no.:10.01.06.00902

<https://www.schmalz.com/10.01.06.00902>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bellows
Suction Cups SAOB HT2 (Oval, 1.5 Folds) > SAOB 140x70 NBR-60 G1/4-IG

Bellows suction cup (oval) for high dynamic on curved, oily surfaced workpieces



Dimensions (LxB): 140 x 70

Suction cup material: Nitrile rubber NBR


Material hardness [Shore A]: 60 Shore A

Nipple material: Nickel plated

Connection: G1/4-IG

Number of folds: 1.5

Design Data



Attribute	Value
B1	67 mm
Bmax(S)	75 mm
Bs	70.10 mm
dn	8 mm
G1	G1/4"-F
H	47 mm
L1	126 mm
LG1	8 mm
Lmax(S)	146 mm
Ls	141.10 mm
SW1	17 mm
Z (Stroke)	16.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	165 N
Pull-off force	355.20 N
Lateral force	472.70 N
Lateral force (oily surface)	245.60 N
Volume	106 cm ³

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Bellows suction cup (oval)

SAOB 140x70 NBR-60 G1/4-IG

Part no...:10.01.06.00902

<https://www.schmalz.com/10.01.06.00902>

Curve radius (min) (convex)	70 mm
Hose diameter (rec.) d	6 mm
Dimensions (LxB)	140 x 70
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A
Number of folds	1.50
Weight	120.70 g
Product family	SAOB

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m